





RoHS

REV.	ECN. #	DESCRIPTION	NAME	DATE
A0		NEW RELEASE	LIHUAMING	2024. 01. 26



MILLIMETERS	INCH	东莞市金比莱五金塑胶科技有限公司 DongGuan JinBiLai Metal Plastic TechnologyCo.,Ltd			
X. ° ±2°	X. ° ±2°				
.X ±0.30	.X ±0.012				
.XX ±0.20	.XX ±0.008				
.XXX ±0.10	.XXX ±0.004				
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co., Ltd. COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co., Ltd.		TITLE		3. 0H No-Push 双层分体式SIM卡座	DR
		PART NO.		102015942-A	CHKD
		PRO J.	PAGE 1/3	UNITS mm	APPD
		SIZE	A4	SCALE 1:1	DIS NO. SM020-00A<客户图>

RoHS



REV.

ECN. #

DESCRIPTION

NAME

DATE

A0

NEW RELEASE

LIHUAMING

2024. 01. 26

NOTES:

1.MATERIAL:

1.1.Housing:HI-TEMP Plastic,UL94V-0,Black;

1.2.Terminal:Copper alloy,

1.3 Shell:Stainless Steel,

2.FINISH:

2.1 Terminal: G/F Plated on the contact area,G/F plated on the solder tails underplated over nickel;

2.2 Shell: G/F plated on the solder tails underplated over nickel;

3. Electrical Performance:

3.1 Contact Resistance:100mΩ Max


3.2 Dielectric Withstanding Voltage:350V AC rms for 1 minut

3.3 Insulation Resistance:1000 MΩ Min

4. Mechanical Performance:



4.1 Durability:5000 cycles;

UPPER CARD




C1	C1:VCC
C2	C2:RST
C3	C3:CLK
C4	C4:RESERVED
C5	C5:GND
C6	C6:VPP
C7	C7:I/O
C8	C8:RESERVED

SIM CARD CIRCUIT



LOWER CARD



MILLIMETERS	INCH
X. ° ±2°	X. ° ±2°
.X ±0.30	.X ±0.012
.XX ±0.20	.XX ±0.008
.XXX ±0.10	.XXX ±0.004

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co., Ltd. COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co., Ltd



东莞市金比莱五金塑胶科技有限公司


DongGuan JinBiLai Metal Plastic TechnologyCo.,Ltd

TITLE	3. 0H No-Push 双层分体式SIM卡座	DR	
PART NO.	102015942-A	CHKD	
PRO J.	PAGE 2/3 UNITS mm APPD		
SIZE	A4 SCALE 1:1 DIS NO.	SM020-00A<客户图>	


F




Direction of use



2、Loading and packing method



3、Total packaging:6300PCS/Box



MILLIMETERS		INCH		东莞市金比莱五金塑胶科技有限公司 DongGuan JinBiLai Metal Plastic TechnologyCo.,Ltd					
X. ° ±2°	X. ° ±2°	TITLE 3.0H No-Push 双层分体式SIM卡座					DR		
.X ±0.30	.X ±0.012								
.XX ±0.20	.XX ±0.008								
.XXX ±0.10	.XXX ±0.004								
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co., Ltd COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd		PART NUM.	102015942-A			CHKD			
		PRO J.	PAGE	3/3	UNITS	mm	APPD		
			SIZE	A4	SCALE	1:1	DIS NO.	SMO20-00A<客户图>	