









Specifications
Current Rating:1.0A AC/DC
Voltage Rating:250V AC/DC
Contact Resistance:30m ohm. Max
Insulation Resistance:100Mohm min
Withstanding Voltage:250V(r.m.s) For one Minute
Operating Temperature Range:-40°C to 85°C
Materials:
Insulator:High Temp. Plastic(LCP UL94V-0)
Color:Natural Color
Contact :Phosphor Bronze
Plated:Gold Plated



Number of Position	MATED HEIGHT			
	SOCKET H1	PLUG H2		
		6.35	8.35	
		5.35	7.65	9.65
		10.35	12.65	14.65
A	B	C	D	
20	13.90	9.00	12.58	12.40
30	18.90	14.00	17.58	17.40
40	23.90	19.00	22.58	22.40
50	28.90	24.00	27.58	27.40
60	33.90	29.00	32.58	32.40
64	35.90	31.00	34.58	34.40
70	38.90	34.00	37.58	37.40
80	43.90	39.00	42.58	42.40
84	45.90	41.00	44.58	44.40
90	48.90	44.00	47.58	47.40
100	53.90	49.00	52.58	52.40
110	58.90	54.00	57.58	57.40
120	63.90	59.00	62.58	62.40





Recommended PC board pattern
(TOP VIEW)








LXW 连兴旺电子(深圳)有限公司 connectivity LXWCONN ELECTRONICS (SHENZHEN) CO., LTD					
制图 (DR):	Jerry 2020.03.21	品名(TITLE):	1.0mm BTB PLUG		
审核 (CHD):		料号(PART NO):	LB11** - ***P - WOR		
核准 (APPD):	Tong 2020.03.21	比例(SCALE):	1:1	单位(UNITS):	mm
		张数(SHEET):	1 OF 1	图幅(SIZE):	A4

修订 SER	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE



Specifications
Current Rating:1.0A AC/DC
Voltage Rating:250V AC/DC
Contact Resistance:40m ohm. Max
Insulation Resistance:1000Mohm min
Withstanding Voltage:250V(r.m.s) For one Minute
Operating Temperature Range:-40°C to 85°C
Materials:
Insulator:High Temp. Plastic(LCP UL94V-0)
Color:Natural Color
Conact :Phosphor Bronze
Plated:Gold Plated



Recommended PC board pattern
(TOP VIEW)

Number of Position	MATED HEIGHT			
	SOCKET H1	PLUG H2		
		6.35	8.35	
		5.35	7.65	9.65
		10.35	12.65	14.65
20	13.90	9.00	12.22	12.40
30	18.90	14.00	17.22	17.40
40	23.90	19.00	22.22	22.40
50	28.90	24.00	27.22	27.40
60	33.90	29.00	32.22	32.40
64	35.90	31.00	34.22	34.40
70	38.90	34.00	37.22	37.40
80	43.90	39.00	42.22	42.40
84	45.90	41.00	44.22	44.40
90	48.90	44.00	47.22	47.40
100	53.90	49.00	52.22	52.40
110	58.90	54.00	57.22	57.40
120	63.90	59.00	62.22	62.40

L B I I * * - * * * S - W O R

PACKING: R:REEL
O:STANDARD SPECIFICATIONS
COLOR:BLACK/WHITE
S:SOCKET
PIN
PLATING: G:GOLD FLASH
HEIGHT:53-5.35H, A0-10.35H
1:1.0 BTB
LXWCONN BTB CONNECTOR SERIES

LXW 连兴旺电子(深圳)有限公司
connectivity LXWCONN ELECTRONICS (SHENZHEN) CO., LTD

RoHS Compliant
2013/05/EC



修订 SER	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE

一般公差 GENERAL TOLERANCE
.X ±0.35
.XX ±0.10
.XXX ±0.06
ANGLES ±1°

制图 (DR): Jerry 2020.03.21	品名(TITLE): 1.0mm BTB SOCKET
审核 (CHD): Tong 2020.03.21	料号(PART NO): LB11**-*S-WOR
核准 (APPD):	比例(SCALE): 1:1
	单位(UNITS): mm
	张数(SHEET): 1 OF 1
	图幅(SIZE): A4