








NOTES

1.MATERIAL

1-1 HOUSING: LCP THERMOPLASTIC. UL94V-0. COLOR: BLACK.

1-2 CONTACT: HIGH-PERFORMANCE COPPER ALLOY.

1-3 LATCH: STAINLESS STEEL.

1-4 PEG: STAINLESS STEEL.

2.FINISH


2-1 CONTACT: GOLD PLATING 1~3u" ON CONTACT AREA
AND 1~3u" GOLD PLATING ON SOLDER AREA
NICKEL 50u"~150u" UNDER-PLATING ALL OVER

2-2 PEG: 50~150u" TIN PLATING OVER
50~150u" NICKEL UNDER-PLATING ALL OVER

3.MSL LEVEL: MSL(MOISTURE SENSITIVITY LEVEL)=1.

4.IR REFLOW:

THE PEAK TEMPRATURE ON THE BOARD SHALL BE
MAINTAINED FOR 10 SECONDS AT 260±5°C.

TOLERANCE		UMax conn 东莞市友贸实业有限公司 DONGGUAN UMAX ENTERPRISE LIMITED		TITLE: DDR4 SODIMM 8.0H 260PIN REVERSE G/F TYPE.				
LINEAR	ANGLES			PART NO. D4260-8001RR				
X,±0.40	X°,± 3°			DWG NO. C-D4260-80R				
.X±0.30	.X°±			APPD: Jason	MAT'L:		UNITS	SCALE
.XX±0.20	.XX°±	CHKD: Schumi	FINISH:	MM	1 : 1		1 OF 2	A0
.XXX±0.10	.XXX°±	DRWN:Lei Songping	Q'TY:					

CUSTOMER













TABLE 2

4.70	1.70	1.70	9.30	3.70
3.70	1.20	1.20	8.80	4.20
DIM. H	DIM. A	DIM. B	DIM. C	DIM. D

TOLERANCE		UMax conn 东莞市友贸实业有限公司 DONGGUAN UMAX ENTERPRISE LIMITED		TITLE: DDR4 SODIMM 8.0H 260PIN REVERSE G/F TYPE.						
LINEAR	ANGLES			PART NO. D4260-8001RR						
X,±0.40	X°,± 3°			DWG NO. C-D4260-80R						
.X,±0.30	.X°±			APPD:	Jason	MAT'L:		UNITS	SCALE	SHEET
.XX,±0.20	.XX°±	CHKD:	Schumi	FINISH:			MM	1 : 1	2 OF 2	A0
.XXX,±0.10	.XXX°±	DRWN:	Lei Songping	Q'TY:						