



Recommended PC board pattern
(TOP VIEW)

SPECIFICATIONS


- 1.CURRENT RATING: 1.34A .
- 2.VOLTAGE RATING 155 VAC.
- 3.OPERATING TEMPERATURE RANGE:-55°C TO +125°C
- 4.HIGH-SPEED CHANNEL PERFORMANCE 56Gbps



STACK HEIGHT				
ADM6	F	G	H	R
1.5	3.40	2.90	0.800	3.32
3.5	5.40	4.90	2.800	15.32
6.5	8.40	7.90	5.800	8.32
8.5	10.40	9.90	7.800	10.32

STACK HEIGHT				
ADF6	ADM6			
	1.5	3.5	6.5	8.5
3.5	5.00	7.00	10.00	12.00
7.5	9.00	11.00	14.00	16.00

Circuits	A	B	C	D
4x10	11.07	5.715	8.395	8.52
4x20	17.42	12.065	14.745	14.87
4x30	23.77	18.415	21.095	21.22
4x40	30.12	24.765	27.445	27.57
4x50	36.47	31.115	33.795	33.92
4x60	42.82	37.465	40.145	40.27
4x70	49.17	43.815	46.495	46.62
4x80	55.52	50.165	52.845	52.97
4x90	61.87	56.515	59.195	59.32
4x100	68.22	62.865	65.545	65.67



LIB12171*-*-*P-BIXIR

PACKING: R:REEL
O: WITH POSITIONING POSTS
1:WITHOUT POSITIONING POSTS
B:BLACK
P-PLUG
PIN
PLATING: F:10u"Min镀金
E:30 μ"Min镀金
HEIGHT:15-1.5H,35-3.5H,65-6.5H,85-8.5H
7:0.635 BTB
LXWCONN BTB CONNECTOR SERIES

LXW 连兴旺电子(深圳)有限公司
connectivity LXWCONN ELECTRONICS (SHENZHEN) CO., LTD

PII
制图 (DR): 2022.06.16
品名 (TITLE): ADM6 0.635mm BTB PLUG
审核 (CHKD):
料号 (PART NO): LB27XX-XXXX-BXR
比例 (SCALE): 1:1
单位 (UNITS): mm
张数 (SHEET): 1 OF 3
图幅 (SIZE): A4



A0	NEW EDITION	PII	2022.06.16
修订	修改摘要	签名	日期
SER	REVISION DESCRIPTION	SIGNATURE	DATE

一般公差
GENERAL TOLERANCE
XX ±0.30
XX ±0.13
XX ±0.05
ANGLES ±2°
版本 A
(REV)