





Recommended PC board pattern
(TOP VIEW)



- SPECIFICATIONS
- 1.CURRENT RATING: 1.4A .
 - 2.VOLTAGE RATING 300 VDC.
 - 3.OPERATING TEMPERATURE RANGE:-55°C TO +125°C
 - 4.HIGH-SPEED CHANNEL PERFORMANCE 56Gbps

LB3***-***P-BOR01

流水号
PACKING: R:REEL
O:STANDARD SPECIFICATIONS
COLOR:BLACK
P: PLUG
PIN
G:GOLD FLASH
3:PLATING 3u"Min GOLD. F:PLATING 10u"Min GOLD.
PLATING: D:PLATING 15u"Min GOLD. E:PLATING 30u"Min GOLD.
HEIGHT:20-2.0H, 50-5.0H, 80-8.0H, 90-9.0H,
30.8 BTB
LXWCONN BTB CONNECTOR SERIES

POSITION	A	B	C	D
10	10.00	8.20	3.20	6.80
14	11.60	9.80	4.80	8.40
20	14.00	12.20	7.20	10.80
22	14.80	13.00	8.00	11.60
24	15.60	13.80	8.80	12.40
26	16.40	14.60	9.60	13.20
30	18.00	16.20	11.20	14.80
40	22.00	20.20	15.20	18.80
50	26.00	24.20	19.20	22.80
60	30.00	28.20	23.20	26.80
70	34.00	32.20	27.20	30.80
80	38.00	36.20	31.20	34.80
100	46.00	44.20	39.20	42.80
120	54.00	52.20	47.20	50.80
140	62.00	60.20	55.20	58.80
150	66.00	64.20	59.20	62.80
200	86.00	84.20	79.20	82.00

HEIGHT	H	H1
2.00	1.61	5.97
3.00	2.61	6.97
5.00	4.61	8.91
8.00	7.61	11.91
9.00	8.61	12.91

MATED HEIGHT			
ERM8 LEAD STYLE	ERF8 LEAD STYLE		
	5.0	7.0	9.0
2.0	7.00	9.00	11.00
3.0	8.00		
5.0	10.00	12.00	14.00
8.0	13.00	15.00	17.00
9.0	14.00	16.00	18.00

LXW 连兴旺电子(深圳)有限公司
connectivity LXWCONN ELECTRONICS (SHENZHEN) CO., LTD

制图 (OR): Jerry 2020.07.04 品名 (TITLE): ERM8 0.8 PITCH BTB PLUG
审核 (CHKD): 料号 (PART NO): LB3***-***P-BOR01
核准 (APPD): Tong 2020.07.04 比例 (SCALE): 1:1 单位 (UNITS): mm 张数 (SHEET): 1 OF 1 图幅 (SIZE): A4

修订 SER	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE

一般公差
GENERAL TOLERANCE
.X ±0.35
.XX ±0.25
.XXX ±0.10
ANGLES ±1°

