




SPECIFICATIONS
1.CURRENT RATING: 1.0A
2.VOLTAGE RATING 240VAC
3.OPERATING TEMPERATURE RANGE:-55°C TO +125°C
4.OPERATING HUMIDITY RANGE:90% TO 95%.
5.WITHSTANDING VOLTAGE:700V AC/MINUTE.

L B 1 9 * * - * * * S - B * R 0 2

02:95.5% TIN/3.8% SILVER/.7% COPPER CHARGE TAIL
PACKING: R:REEL
ROWS:4:4ROWS,5:5ROWS,6:6ROWS,8:8ROWS, A:10ROWS.C:12ROWS.D:14ROWS
COLOR:BLACK/WHITE
S: SOCKET
PIN
PLATING: G:GOLD FLASH F:10u"Min镀金 D:15u"Min镀金 E:30u"Min镀金
HEIGHT:50-5.05H, 60-6.05H, 65-6.55H,75-7.54H.
9:1.27 BTB
LXWCONN BTB CONNECTOR SERIES

TABLE 2			TABLE 4	
ROWS	W	G	POSITION	COPLANARITY
4	5.66	2.01	10 PIN	0.15
5 OR 6	8.20	3.05	30 PIN	0.20
8	10.74	3.05	40 PIN	0.23
10	13.28	3.05	50 PIN	0.23
12	15.82	3.05		
14	18.36	3.05		

TABLE 3				
No OF ROWS	A	B	C	D
10	18.52	17.02	11.43	16.28
15	24.87	23.37	17.78	22.63
19	29.95	28.45	22.86	27.71
20	31.22	29.72	24.13	28.98
25	37.57	36.07	30.13	35.33
30	43.92	42.42	36.83	41.68
40	56.62	55.12	49.53	54.38
50	69.32	67.82	62.23	67.08

TABLE 5 STACK HEIGHT				
	5.0	6.0	6.5	7.5
2.0	7.00	8.00	8.50	9.50
3.0	8.00	9.00	9.50	10.50
3.5	8.50	9.50	10.00	11.00
5.5	NA	NA	12.00	NA

TABLE 1	
HEIGHT	H
5.0	5.05
6.0	6.05
6.5	6.55
7.5	7.54

RoHS Compliant 2013/95/EC

修订 SER	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE
-----------	------------------------------	-----------------	------------

一般公差
GENERAL TOLERANCE
.X ±0.35
.XX ±0.25
.XXX ±0.10
ANGLES ±1°

版本 (REV) A

制图 (DR): Jerry 2020.06.21

品名 (TITLE): SEAF 1.27 PITCH SOCKET

审核 (CHKD):

料号 (PART NO): LB19**-***S-B*R02

核准 (APPD): Tong 2020.06.21


比例 (SCALE): 1:1

单位 (UNITS): mm

张数 (SHEET): 1 OF 2

图幅 (SIZE): A4

连兴旺电子(深圳)有限公司
LXWCONN ELECTRONICS (SHENZHEN) CO., LTD



Recommended PC board pattern (TOP VIEW)

RoHS
Compliant
2013/95/EC



连兴旺电子(深圳)有限公司

LXWCONN ELECTRONICS (SHENZHEN) CO., LTD

一般公差
GENERAL TOLERANCE
.X ± 0.35
.XX ± 0.25
.XXX ± 0.10
ANGLES $\pm 1^\circ$

制图 (DR): Jerry
2020.06.21

品名 (TITLE): 1.27 PITCH SOCKET PCB

审核 (CHKD):

料号 (PART NO): LB19**--***S-B*R02

核准 (APPD): Tong
2020.06.21

比例 (SCALE): 1:1
单位 (UNITS): mm
张数 (SHEET): 2 OF 2
图幅 (SIZE): A4

修订 SER	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE

版本 (REV): A

