




Recommended PC board pattern
(TOP VIEW)

- SPECIFICATIONS
- 1.CURRENT RATING: 1.34A .
 - 2.VOLTAGE RATING 155 VAC.
 - 3.OPERATING TEMPERATURE RANGE:-55°C TO +125°C
 - 4.HIGH-SPEED CHANNEL PERFORMANCE 56Gbps



ADF6	K	L	H
3.5	3.23	3.65	3.73
7.5	7.23	7.65	7.73

ADF6	STACK HEIGHT			
	ADM6			
	1.5	3.5	6.5	8.5
3.5	5.00	7.00	10.00	12.00
7.5	9.00	11.00	14.00	16.00



LB12171*-***S-BX1R

PACKING: R:REEL
O: WITH POSITIONING POSTS
1:WITHOUT POSITIONING POSTS
B:BLACK
S:SOCKET
PIN
PLATING: F:10u"Min镀金
E:30 u"Min镀金
HEIGHT:35-3.5H,75-7.5H
7:0.635 BTB
LXWCONN BTB CONNECTOR SERIES

Circuits	A	B	C	D
4x10	11.07	5.715	8.595	8.52
4x20	17.42	12.065	14.945	14.87
4x30	23.77	18.415	21.295	21.22
4x40	30.12	24.765	27.645	27.57
4x50	36.47	31.115	33.995	33.92
4x60	42.82	37.465	40.345	40.27
4x70	49.17	43.815	46.695	46.62
4x80	55.52	50.165	53.045	52.97
4x90	61.87	56.515	59.395	59.32
4x100	68.22	62.865	65.745	65.67

连兴旺电子(深圳)有限公司
connectivity LXWCONN ELECTRONICS (SHENZHEN) CO., LTD



A0	NEW EDITION	PII	2022.06.16
修订 SER	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE

一般公差
GENERAL TOLERANCE

XX ±0.30
XX ±0.13
XX ±0.05
ANGLES ±2°

版本 A
(REV)

制图 (DR): 2022.06.16	品名 (TITLE): ADF6 0.635mm BTB SOCKET
审核 (CHKD):	料号 (PART NO): LB27XX-XXXX-BXR
核准 (APPD):	比例 (SCALE): 1:1
	单位 (UNITS): mm
	张数 (SHEET): 1 OF 3
	图幅 (SIZE): A4