








MATING: ① INSERTING → ② ROTATING → ③ FIXED
UNMATING: ④ UNFIXED → ⑤ ROTATING → ⑥ WITHDRAWING

MATING/UNMATING VIEW
SCALE 2:1

NOTES

1.MATERIAL

- 1-1 HOUSING: LCP THERMOPLASTIC. UL94V-0. COLOR: BLACK.
- 1-2 CONTACT: HIGH-PERFORMANCE COPPER ALLOY.
- 1-3 LATCH: STAINLESS STEEL.
- 1-4 PEG: STAINLESS STEEL.

2.FINISH

- 2-1 CONTACT: GOLD PLATING 1~3u" ON CONTACT AREA AND 1~3u" GOLD PLATING ON SOLDER AREA NICKEL 50u"~150u" UNDER-PLATING ALL OVER
- 2-2 PEG: 50~150u" TIN PLATING OVER 50~150u" NICKEL UNDER-PLATING ALL OVER

3.MSL LEVEL: MSL(MOISTURE SENSITIVITY LEVEL)=1.

4.IR REFLOW:

THE PEAK TEMPRATURE ON THE BOARD SHALL BE MAINTAINED FOR 10 SECONDS AT 260±5°C.

TOLERANCE

LINEAR ANGLES

X±0.40 X°± 3°

.X±0.30 .X°±

.XX±0.20 .XX°±

.XXX±0.10 .XXX°±

UMax 东莞市友贸实业有限公司
conn DONGGUAN UMAX ENTERPRISE LIMITED

APPD: Jason

MAT'L:

CHKD: Schumi

FINISH:


DRWN: Lei Songping

Q'TY:

TITLE: DDR4 SODIMM
4.0H 260PIN STANDARD G/F TYPE.

PART NO. D4260-4001SR

DWG NO. C-D4260-40S



UNITS	SCALE	SHEET	REV
MM	1 : 1	1 OF 2	A0

A0	-----	FENG.PF	Apr.11.2023
REV	ECN NO.	NAME	DATE

