







- SPECIFICATIONS
- 1.CURRENT RATING: 0.5A .
 - 2.VOLTAGE RATING 60V AC/DC.
 - 3.TEMPERATURE RANGE:-55°C TO +125°C
 - 4.CONTACT RESISTANCE: 80mΩ MAX.
 - 5.INSULATION RESISTANCE:500 MΩ MIN.
 - 6.WITHSTANDING VOLTAGE:150V AC/MINUTE.



L B 3 5 * * * * P W * R

PACKING: R:REEL
0:WITH POSITIONING POSTS
1:WITHOUT POSITIONING POSTS
COLOR:WHITE

P: PLUG

PIN

PLATING: G:GOLD FLASH


HEIGHT:24--2.40H,29--2.90H,34--3.40H

5: 0.5BTB

LXWCONN BTB CONNECTOR SERIES

H	C	D
3.0mm	2.40	0.85
3.5mm	2.90	1.35
4.0mm	3.40	1.85

PIN	A	B
20	8.20	4.50
22	8.70	5.00
30	10.70	7.00
34	11.70	8.00
40	13.20	9.50
50	15.70	12.00
60	18.20	14.50
70	20.70	17.00
80	23.20	19.50
100	28.20	24.50
120	33.20	29.50



Recommended PC board pattern
(TOP VIEW)

LXW 连兴旺电子(深圳)有限公司
connectivity LXWCONN ELECTRONICS (SHENZHEN) CO., LTD



修订 SER	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE

版本 (REV)	一般公差 GENERAL TOLERANCE
A	±0.35
X	±0.25
XX	±0.20
XXX	±0.10
ANGLES	±1°

制图 (DR): Jerry 2021.09.21	品名 (TITLE): AXK 0.50mm BTB PLUG
审核 (CHKD): Tong 2021.09.21	料号 (PART NO): LB35**-***P-W*R
核准 (APPD):	比例 (SCALE): 1:1
	单位 (UNITS): mm
	张数 (SHEET): 1 OF 1
	图幅 (SIZE): A4