




Note:

Mechanical

Mating force:40.0kgf max

Unmating force:4.4kgf Min

Durability:30Cycles

Electrical

Current Rating:0.5A max. Percontact

Contact Resistance:55mΩ max(Initial),75mΩ max(After)

Dielectric Withstanding Voltage:200VAC

Insulation Resistance 100mega ohms min. at 500 VDC

Physical

Housing:thermoplastic, UL 94V-0 rated,inWhite Color

Contact: Copper alloy

Operating Temperature:-40°C to +85°C

PART NO.:

LB 2XX-GXXS-B0R

PACKING: R:REEL

0:MYLAR

COLOR:BLACK

SOCKET

PIN

PLATING: G:GOLD FLASH;A:3u";B:10u"

0.5 BTB

MATING HEIGHT:54--5.4H

LXWCONN BTB CONNECTOR SERIES