




RoHS





PCB Layout(Pattern side)



Circuit Diagram

TOTAL HEIGHT		
Code	H	L
038	3.8	3.15
043	4.3	3.65



Product No. : TS-043-□□-□□

型号:

产品高度 (H) :
038=3.8mm
043=4.3mm

□: 包装方式
-P=编带 (非编带, 不启用)
□: 弹片
D2=SUS/1PCS

操作力度:
180=180gf±50gf
250=250gf±50gf

Ⓔ	Terminal		2	Phosphours copper	Silvering
Ⓓ	Reed		1	SUS	Silver Covered
Ⓒ	Button		1	PPA	Black
Ⓑ	Cover		1	Brass	Plating Cu Sn
Ⓐ	Base		1	PPA	Black
NO.	Name	Number	Qty	Materil	Remarks

ZHONGDI®
众迪

Zhongdi Electronic Technology Co., Ltd

design	date	name	TACT SWITCHS
Review	date	model	TS-043-□□-D□
Approved	date		

Drawing number: A4

modify Review Approved

Tolerance not specified

Proportion

1:1

unit

mm

gape number

A4


项 目 Item	技术参数 Technical Parameter	标 准 Standard
电气性能 Electrical Properties	额定电流 Rated Current:	50mA
	额定电压 Rated voltage:	DC 12V
	接触电阻 Contact resistance:	≤100mΩ
	绝缘电阻 Insulation Resistance:	DC 250V 1 min ≥100MΩ
机械性能 Mechanical Properties	耐压强度 Compressive strength:	AC 250V 50Hz/1 min
	机械寿命 Mechanical life:	100,000 cycles Min
环境性能 Environmental	操作行程 Operation Stroke:	0.20±0.10mm
	工作温度 Operation temperature:	-25℃~ +75℃
可靠性特性 Reliability Characteristics	使用湿度 Use humidity:	≤85% RH
	回流焊 Reflow Soldering:	≤260℃ 时间 Time 3s
	波峰焊 Wave soldering:	
应用领域 Application area	手工焊 Manual welding:	≥260℃ 时间 Time 3s
	影音产品、电子玩具、数码产品、通讯产品、安防产品等. Audiovisual products, electronic toys, digital products, communication products, security products, etc	



绝缘电阻测量仪




直流低电阻测试仪




耐电压测试仪



回流焊机



二次元测量仪



高精密寿命测试仪



盐雾测试仪



按键荷重曲线仪

ZHONGDI® 众迪										Zhongdi Electronic Technology Co., Ltd																					
design			date			name			TACT SWITCHS																						
Review			date																												
Approved			date			name			TS-043-□□-D□																						
number:																															
1:1		unit		mm		gape		number												A4											