








REV	ECN NO.	LOCAS.	DESCRIPTION	DATE	DESIGN
A			NEW DRAWING		



Note:

- Material
 - Housing: LCP UL94-V0 Color:Black or White
 - Actuator: LCP OR PA9T UL94-V0 Color:Black.
 - Contact: Phosphor Bronze.
 - LEG: Phosphor Bronze.
- Plating
 - Contact: See Part Number.
 - LEG: Matte Tin Plating Over Nickel.
- Rating:
 - Operating Voltage: 30V AC/DC.
 - Current Rating: 0.2A AC/DC.
 - Operating Temperature:-55°C~+85°C.


Applicable FPC



Long Cover type

No. of Contacts	Dimension					
	A	B	C	D	E	F
09	4.30	1.80	2.40	3.03	3.75	3.00
11	4.90	2.40	3.00	3.63	4.35	3.60
13	5.50	3.00	3.60	4.23	4.95	4.20
15	6.10	3.60	4.20	4.83	5.55	4.80
17	6.70	4.20	4.80	5.43	6.15	5.40
19	7.30	4.80	5.40	6.03	6.75	6.00
21	7.90	5.40	6.00	6.63	7.35	6.60
23	8.50	6.00	6.60	7.23	7.95	7.20
25	9.10	6.60	7.20	7.83	8.55	7.80
27	9.70	7.20	7.80	8.43	9.15	8.40
29	10.30	7.80	8.40	9.03	9.75	9.00
31	10.90	8.40	9.00	9.63	10.35	9.60
33	11.50	9.00	9.60	10.23	10.95	10.20
35	12.10	9.60	10.20	10.83	11.55	10.80
39	13.30	10.80	11.40	12.03	12.75	12.00
41	13.90	11.40	12.00	12.63	13.35	12.60
45	15.10	12.60	13.20	13.83	14.55	13.80
51	16.90	14.40	15.00	15.63	16.35	15.60

Long Cover type



FPC/FFC Insert Direction
Recommended P.C.B Layout

DESIGN:	Xiping Huang			
CHECK:	Ke Tian			
APPROVED:	Youquan Xu			
DIM	TOL	DIM	TOL	
X.	±0.25	X°	±3.0°	
X.X	±0.20	X.X°		
X.XX	±0.15	X.XX°		
X.XXX		X.XXX°		

 广东国连电子有限公司
GUANGDONG GUOLIAN ELECTRONICS CO.,LTD

TITLE: 0.3前插后掀H1.0

PART NO. 0310B-GX-NPWB-GF-***


REV. A	SCALE: N/A	UNIT: mm	SHEET: 1/1	
--------	------------	----------	------------	---

REV	ECN NO.	LOCAS.	DESCRIPTION	DATE	DESIGN
A			NEW DRAWING		


EMBOSSED TAPE PACKING

FPC 0.3Pitch 1.0H ZIF R/A Double Contact
Connector SMT Type


PULL OUT DIRECTION




SCALE 1:4



PULL OUT DIRECTION




PULL OUT DIRECTION

16PCS PRODUCTS
EMPTY (START)
前面空16个穴不装产品16PCS PRODUCTS
EMPTY (END)
后面空16个穴不装产品Ref 128mm Lenght cover tape
后面留大约128mm盖带CASED 4000PCS PRODUCTS
装4000PCS产品

NOTE:

- 1.10 Sprocket hole pitch cumulative tolerance ± 0.20 .
- 2.Carrier camber is within 1mm in 100mm.
- 3.Material: black conductive polystyrene alloy.
- 4.Material Thickness: 0.3 ± 0.05 mm.
- 5.All dimensions meet EIA-481-B requirements.
- 6.5000pcs Pef Reel.
- 7.For tape width(dim W)12,16 and 24mm pilot holes are provided on one sides.
For tape width(dim W)32, 44mm pilot holes are provided on both sides.



DESIGN:	Xiping Huang				广东国连电子有限公司			
CHECK:	Ke Tian				GUANGDONG GUOLIAN ELECTRONICS CO., LTD			
APPROVED:	Youquan Xu				TITLE:			
DIM	TOL	DIM	TOL	0.3前插后掀H1.0				
X.	±0.25			PART NO.				
X.X	±0.20	X°.	±3.0°	0310B-GX-NPWB-GF-**-				
X.XX	±0.15	X.X°		REV. A	SCALE: N/A	UNIT: mm	SHEET: 1/1	
X.XXX		X.XX°						

PIN NO.	W	A	B	C	PCS /REEL	REEL/CARTON	SUM(PCS)
9PIN~25PIN	16	20.5	7.50	-	4000	15	60000
31PIN~45PIN	24	28.5	11.5	-	4000	10	40000
51PIN	32	36.5	14.2	28.4	4000	8	32000