









REV	ECN NO.	LOCAS.	DESCRIPTION	DATE	DESIGN
A			NEW DRAWING		




- Note:
- 1.Material
 - 1.1: Housing: High Temp-plastic
 - 1.2: Actuator: High Temp -plastic
 - 1.3: Contact: Copper Alloy
 - 1.4: LEG: Copper Alloy
 - 2.Plating
 - 2.1: Contact: See Part Number.
 - 2.2: LEG: Matte Tin Plating Over Nickel.
 - 3.Rating:
 - 3.1: Operating Voltage: 30V AC/DC.
 - 3.2: Current Rating: 0.2A AC/DC.
 - 3.3: Operating Temperature:-55°C~+85°C.



Applicable FPC


FPC/FFC Insert Direction
Recommended P.C.B Layout

DESIGN:		Xiping Huang			广东国连电子有限公司				
CHECK:		Ke Tian			GUANGDONG GUOLIAN ELECTRONICS CO.,LTD				
APPROVED:		Youquan Xu		TITLE:					
DIM	TOL	DIM	TOL	0.5翻盖H1.0 大锁扣					
X.	±0.25			PART NO.					
X. X	±0.20	X° .	±3.0°	0509B-6RL-GF-**					
X. XX	±0.15	X. X°		REV. A	SCALE: N/A	UNIT: mm	SHEET: 1/1		
X. XXX		X. XX°							
		X. XXX°							



NOTE:

- 1.10 Sprocket hole pitch cumulative tolerance ± 0.20 .
- 2.Carrier camber is within 1mm in 100mm.
- 3.Material: black conductive polystyrene alloy.
- 4.Material Thickness: 0.3 ± 0.05 mm.
- 5.All dimensions meet EIA-481-B requirements.
- 6.5000pcs Pef Reel.
- 7.For tape width(dim W)16 and 24mm
pilot holes are provided on one sides.
For tape width(dim W)32, 44 and 56mm
pilot holes are provided on both sides.



PIN NO.		W	A	B	C	? PCS/Reel	Reel/Carton	Sum(PCS)
06PIN		20.5	16	7.50	-	5000	13	65000

DESIGN:		Xiping Huang		 广东国连电子有限公司 GUANGDONG GUOLIAN ELECTRONICS CO., LTD
CHECK:		Ke Tian		
APPROVED:		Youquan Xu		TITLE:
DIM	TOL	DIM	TOL	0.5翻盖H1.0 大锁扣
X.	±0.25			PART NO.
X. X	±0.20	X° .	±3.0°	
X. XX	±0.15	X. X°		REV. A
X. XXX		X. XX°		
		X. XXX°		SCALE:
				N/A
				UNIT:
				mm
				SHEET:
				1/1
				