

A

B





C

D

E

F

修 订 REV NO	标 记 MARK	修 改 描 要 REVISION DESCRIPTION	签 名 SIGNATURE	日 期 DATE
		NEW DWG		2016-03-12



PCB LAYOUT

SPECIFICATIONS

Current Rating: 1Amps
Insulator resistance: 5000 Megohms min.
Dielectric Withstaanding: AC 500V
Operating Temperature: -40° TO +105°C
Max Processing Temp: 230° TO 260° for 30-60 seconds
Contact Materiaal: Brass
Plating: Gold Flash
Insulator Material: NYLON-6T

UNSPECIFIED TOLERANCE: ± 0.20

Dimen Sions List

Contacts Per Row	A	B	Contacts Per Row	A	B
2*02	2.54	1.27	2*22	27.94	26.67
2*03	3.81	2.54	2*23	29.21	27.94
2*04	5.08	3.81	2*24	30.48	29.21
2*05	6.35	5.08	2*25	31.75	30.48
2*06	7.62	6.35	2*26	33.02	31.75
2*07	8.89	7.62	2*27	34.29	33.02
2*08	10.16	8.89	2*28	35.56	34.29
2*09	11.43	10.16	2*29	36.83	35.56
2*10	12.70	11.43	2*30	38.70	36.83
2*11	13.97	12.70	2*31	39.37	38.10
2*12	15.24	13.97	2*32	40.64	39.37
2*13	16.51	15.24	2*33	41.91	40.64
2*14	17.78	16.51	2*34	43.18	41.91
2*15	19.05	17.78	2*35	44.45	43.18
2*16	20.32	19.05	2*36	45.72	44.45
2*17	21.59	20.32	2*37	46.99	45.72
2*18	22.86	21.59	2*38	46.99	54.61
2*19	24.13	22.66	2*39	49.53	48.26
2*20	25.40	24.13	2*40	50.80	49.53
2*21	26.67	25.40			



深圳市华德共创科技有限公司

Shenzhen Huade co-create Technology Co.,LTD

电话: 0755-27111216 传真: 0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表				TITLE: 产品名称: 1.27*1.0 SMT 排针PA4.0 PB1.5 PC5.5			
X.X ±0.30	X.X* ±3°	APPD: 核准:		PART NO: 产品编号: HDGC127-PS2-n			
X.XX ±0.20	X.XX* ±2°	CHECK: 校对: 王建业		DATE	SCALE	UNIT	CODE NUMBER
X.XXX ±0.10	X.XXX* ±1°	DRAW: 绘图: 黄艳兰		2016-03-12	1:1	mm	A001