



HSF



ROHS







NOTES:

- 1, BASE"
MAT'L: GLSAA FILED LCP UL 94V-0
- 2, CONTACTS:
MAT'L: 0.15mm TH' K PHOSPHOR BRONZE
FINISH: GOLD FLASH PLATING

Order code:

BT - M - GO - R - CR2450C
① ② ③ ④ ⑤


- ① BT: Coin Cell Holders
② Appearance for the product
M: SMT TYPE
- ③ Contact Plating
SN: Tin
G0: Gold flash
G1: 3U" Gold
G2: 5U" Gold
G3: 10U" Gold
G4: 15U" Gold
G5: 30U" Gold
- ④ Packing method
A: Tray packing
R: Tape & reel packing
- ⑤ Product number
CR2450C



! MOUNTING PAD LAYOUT ZONE FOR OPTIONAL ADHESIVE FIXATION

Unless Otherwise specified tolerance
X. ± 0.35 X. XX: ± 0.20
X. X: ± 0.25 X. XXX: ± 0.15

SCALE: As Shown UNIT: mm
DRAW Lv Xun Hua DATE 29/03/2019
CHECK BobYang DATE 29/03/2019



Antenk®

TITLE: Coin Cell Holders For CR2450

DRAWING NO: BT-M-GO-R-CR2450C

PRODUCT NO: BT-M-GO-R-CR2450C

REV

! ADD MOUNTING PAD LAYOUT

DESCRIPTION

DATE