




HSF



Recommend PCB
Layout

NOTE:

1, Material:

- a. Housing: PA BK V0 GF30.15
- b. Contact: Manganese Steel 
(Surface Plating: Sn 10u")
- See Ordering Information

2, Electric:

- a. Contact Resistance: 30 Milliohms Max
- b. Insulation Resistance: 1000 MEGA OHMS Min
- c. Dielectric Voltage: 500V AC One Sea Level
- d. Operating Temperature: -55° To 105°

Order code:

BT - S - SN - R - CR2430D
① ② ③ ④ ⑤

- ① BT: Coin Cell Holders
- ② Appearance for the product
- ③ Contact Plating

S: 180 TYPE

SN: Tin

G0: Gold flash

G1: 3U" Gold

G2: 5U" Gold

G3: 10U" Gold

G4: 15U" Gold


G5: 30U" Gold

- ④ Packing method
- A: Tray packing
- R: Tape & reel packing

- ⑤ Product number
- CR2430D

Unless Otherwise specified tolerance
X. ±0.35 X.XX: ±0.20
X.X: ±0.25 X.XXX: ±0.15

SCALE: As Shown UNIT: mm
DRAW Wu Feng Rong DATE 10/01/2020
CHECK BobYang DATE 01/13/2019



TITLE:

Coin Cell Holders For CR2430

DRAWING NO:

BT-S-SN-R-CR2430D

PRODUCT NO:

BT-S-SN-R-CR2430D

 Revise Contact Material

19/08/2022

 Revise Dimension Depend Sample

07/02/2022

1

REV

DESCRIPTION

DATE

1

2

3

4

5

6

7

8