


HSF



RoHS



RECOMMEND PCB LAYOUT
COMPOENT SIDE

NOTES

1. MATERIALS:
HOUSING-PBT
CONTACT-PHOSPHOP BRONZE,
2. FLASH:0.25mm MAX
3. CAMBER:0.13mm MAX. DEFORMATION:NA.
WARP:0.13mm MAX. TWIST:NA

Order code:

BT — S — SN — A — CR2330A
① ② ③ ④ ⑤

- ① BT:Coin Cell Holders
- ② Apperance for the product
S:180 TYPE


- ③ Contact Plating
SN: Tin
G0: Gold flash
G1: 3U" Gold
G2: 5U" Gold
G3: 10U" Gold
G4: 15U" Gold
G5: 30U" Gold

- ④ Packing method
A: Tray packing
R: Tape & reel packing

- ⑤ Product number
CR2330A

Unless Otherwise specified tolerance
X. ± 0.35 X. XX: ± 0.20
X. X: ± 0.25 X. XXX: ± 0.15

SCALE: As Shown UNIT: mm
DRAW Mo Guo Xuan DATE 03/15/2019
CHECK BobYang DATE 03/15/2019



Antenk®

TITLE: Coin Cell Holders For CR2330

DRAWING NO: BT-S-SN-A-CR2330A

PRODUCT NO: BT-S-SN-A-CR2330A

△ Revise Dimensions

08/03/2022

REV DESCRIPTION

DATE