









Applicable FPC




SEC A-A



SEC A-A

Long Cover type



FPC/FFC Insert Direction
Recommended P.C.B Layout

Note:

1.Material

- 1.1: Housing: LCP UL94-V0 Color:Black or White
- 1.2: Actuator: LCP OR PA9T UL94-V0 Color:Black.
- 1.3: Contact: Phosphor Bronze.
- 1.4: LEG: Phosphor Bronze.

2.Plating

- 2.1: Contact: See Part Number.
- 2.2: LEG: Matte Tin Plating Over Nickel.

3.Rating:

- 3.1: Operating Voltage: 30V AC/DC.
- 3.2: Current Rating: 0.2A AC/DC.
- 3.3: Operating Temperature:-55°C~+85°C.

No. of Contacts	Dimension					
	A	B	C	D	E	F
09	4.30	1.80	2.40	3.03	3.75	3.00
11	4.90	2.40	3.00	3.63	4.35	3.60
13	5.50	3.00	3.60	4.23	4.95	4.20
15	6.10	3.60	4.20	4.83	5.55	4.80
17	6.70	4.20	4.80	5.43	6.15	5.40
19	7.30	4.80	5.40	6.03	6.75	6.00
21	7.90	5.40	6.00	6.63	7.35	6.60
23	8.50	6.00	6.60	7.23	7.95	7.20
25	9.10	6.60	7.20	7.83	8.55	7.80
27	9.70	7.20	7.80	8.43	9.15	8.40
29	10.30	7.80	8.40	9.03	9.75	9.00
31	10.90	8.40	9.00	9.63	10.35	9.60
33	11.50	9.00	9.60	10.23	10.95	10.20
35	12.10	9.60	10.20	10.83	11.55	10.80
39	13.30	10.80	11.40	12.03	12.75	12.00
41	13.90	11.40	12.00	12.63	13.35	12.60
45	15.10	12.60	13.20	13.83	14.55	13.80
51	16.90	14.40	15.00	15.63	16.35	15.60

Long Cover type

东莞市高钺达电子科技有限公司
惠州市高钺达光电科技有限公司



TITLE: 0.3Pitch 1.0H
品名: ZIF/前插后掀式

一般公差 (TOLERANCE)

APPD:

核准:

CHECK:

校對:

DRAW:

繪圖:

DWG NO:

產品料號: FPCXX-T1S1-0010-A

DATE

SCALE

UNIT

PAGE

20130618

1:1

mm

1/1

