

HSF



CONTACT SURFACE

SOLDER TAIL

1.83±0.25

2.48

3.48

3.18

3.51

3.56MIN

3.96MIN

MTG LAY OUT WHEN USE WITH 127

BATTERY DIA	L
20mm	9.4
24mm	11.4

NOTE:

MATERIAL: 0.15 STAINLESS STEEL FINISH
GOLD-PLATED

COATING PARAMETERS: 4um

TEMPERATURE RANGE: -40° C ~ 270° C

VOLTAGE PARAMETERS : 270V

Order code:

BS — M — SI — R — 126
① — ② — ③ — ④ — ⑤

① BS: Battery contacts

② Appearance for the product
M: SMT TYPE

③ Contact Plating
SI: NICKEL Plated
SN: Tin


G0: Gold flash
G1: 3U" Gold
G2: 5U" Gold
G3: 10U" Gold
G4: 15U" Gold
G5: 30U" Gold

④ Packing method
A: Tray packing
R: Tape & reel packing

⑤ Product number:
126

Unless Otherwise specified tolerance
X. ±0.35 X.XX: ±0.20
X.X: ±0.25 X.XXX: ±0.15

SCALE: As Shown UNIT: mm
DRAW Wu Feng Rong DATE 06/08/2019
CHECK BobYang DATE 06/08/2019



Antenk® ANTENK ELECTRONICS CO., LTD
Http://www.antenk.com
E-mail: sales@antenk.com

TITLE: Battery Contacts 126

DRAWING NO: BS-M-G0-R-126-Z

PRODUCT NO: BS-M-G0-R-126-Z

REV

DESCRIPTION

DATE