



HSF



RoHS



MOUNTING DETAIL



NOTES:

- 1, BASE:
MAT'L: BASE, BLACK PBT UL 94V-0
- 2, TOP CONTACT:
MAT'L: 0.4mm TH'K SPRING STEEL
FINISH: TIN NICKEL PALTE
- 3, BOTTOM CONTACT:
MAT'L: 0.9mm DIA. STEEL
FINISH: TIN PLATE


Order code:

BT — S — SN — R — CR1225B
① ② ③ ④ ⑤

- ① BT: Coin Cell Holders
② Apperance for the product
S:180 TYPE
- ③ Contact PIating
SN: Tin
G0: Gold flash
G1: 3U" Gold
G2: 5U" Gold
G3: 10U" Gold
G4: 15U" Gold
G5: 30U" Gold
- ④ Packing method
A: Tray packing
R: Tape & reel packing
- ⑤ Product number
CR1225B

Unless Otherwise specified tolerance
X. ± 0.35 X. XX: ± 0.20
X. X: ± 0.25 X. XXX: ± 0.15

SCALE: As Shown UNIT: mm
DRAW Mo Guo Xuan DATE 13/03/2019
CHECK BobYang DATE 13/03/2019

**Antenk**®

TITLE: Coin Cell Holders For CR1225

DRAWING NO: BT-S-SN-R-CR1225B

PRODUCT NO: BT-S-SN-R-CR1225B

① Revise Dimensions
DESCRIPTION

08/03/2022
DATE

REV

1 2 3 4 5 6 7 8