







RoHS Compliant



PCB 焊盘区  
下压定位区

RECOMMENDED PCB LAYOUT  
GENERAL TOLERANCE ±0.05

### Specification

#### MATERIAL:

Insulator: High Temperature Thermoplastic, UL 94V-0.  
Contact: Copper Alloy  
SHELL: SUS

#### PLATING:

Contact: Plated 50u'' Ni Overall Contact Au 1U  
Shell: Plated 50u'' Ni Overall  
Plated 1u''Au Selective Contact Area

#### Electrical:

Current Rating :0.5mA AC/DC max.  
Voltage Rating :125V AC/DC  
Ambient Temperature Range :-20° C~+60° C  
Storage Temperature Range :-40° C~+70° C  
Ambient Humidity Range :95% R.H. Max.  
Contact Resistance:100m max. Ω  
Insulation Resistance:1000M min./500VDC  
产品耐温度: 260° C 6s 31.75±0.6  
Mating Cycles:3000Min Insertions

|                                                        |                                                                   |               |                     |              |    |
|--------------------------------------------------------|-------------------------------------------------------------------|---------------|---------------------|--------------|----|
| 深圳市敏连达科技有限公司<br>Shenzhen Minlianda Technology Co.,Ltd. |                                                                   | 品名(ITEM NO)   | MICRO SIM PUSH 6PIN |              |    |
|                                                        |                                                                   | 料号(PART NO)   | MLD-MICRO-6P-H1.35  |              |    |
| 单位(UNIT): MM                                           | 未注公差<br>TOLERANCE UNSPECIFIED                                     | 版次(REV): A/O  | 页次(PAGE):1/1        | 设计 (DESIGN)  | 柯南 |
| 比例(SCALE) 1:1                                          | X.X ± 0.38<br>X.XX ± 0.20<br>X.XXX ± 0.10<br>X' ± 5'<br>X.X' ± 2' | 模号 (MODEL NO) | 图号 (DWG NO)         | 审核 (CHECKED) | 邱敏 |
|                                                        |                                                                   |               |                     | 核准(APPROVED) | 陈镇 |