









RoHS Compliant



CIRCUIT DIAGRAM



RECOMMENDED P.C.B
TOP VIEW

NOTES:

- MATERIAL: SEE "TABLE 1";
- FINISH: SEE "TABLE 1";

3. ELECTRICAL :

- CONTACT CURRENT RATING :DC 30V 0.5A
- INSULATION RESISTANCE :
100 MEGAOHMS MIN.
- DIELECTRIC WITHSTANDING VOLTAGE :
100VAC MIN.

4. MECHANICAL CHARACTERISTICS :

- MATING FORCE: 3~20N.;
- UNMATING FORCE: 3~20N(INITIAL), 2~20N(AFTER 5000 CYCLES);
- DURABILITY : 5,000 MATING CYCLES.
- OPERATING TEMPERATURE : -30°C TO +70°C

TABLE 1:

NO.	PART NAME	QTY	MATERIAL	DESCRIPTION	REMARK
⑤	弹片端子	1	黄铜	镀亮锡	T=0.15mm
④	弹片端子	1	黄铜	镀亮锡	T=0.15mm
③	弹片端子	1	黄铜	镀亮锡	T=0.15mm
②	弹片端子	1	黄铜	镀亮锡	T=0.15mm
①	主体胶芯	1	PPA	黑色	

单位(UNIT): MM	未注公差 TOLERANCE UNSPECIFIED	版次(REV): A/0	品名(ITEM NO)	
			设计 (DESIGN)	柯南
XX	± 0.38		料号(PART NO)	MLD-PJ-320D-4P
XXX	± 0.20		比例(SCALE) 1:1	
XXXX	± 0.10		模号(MODEL NO)	
X'	± 5°		图号(DWG NO)	MLD-2509031032
X.X	± 2°		审核(CHECKED)	邱敏