






RoHS Compliant



规格说明:Specifications:

电气特性:Electrical:

- 额定电流: Current Rating
2.0A/contact terminal
- 额定电压: Voltage Rating
30V DC
- 接触阻抗:Contact Resistance
30 milliohms MAX
- 耐电压:Dielectric Withstanding Voitage:
500 V AC AT Sea Levot
- 绝缘阻抗:Insulation Resistance:
1000MEGA ohms MIN

物理性能:Mechanical:

- 插拔力: Cnector Mate and Unmate Force
Mate force:3.57kgf(MAX)
Unmate force:1.02kgf(MIN)
- 端子保持力: Terminal Retenion
1.2kgf(MIN)

原材料:Matorial:

- 塑胶:Housing:
Hing Temperature Tnermaplastics,
Ul 94V-0 PBT White/Black
- 端子>Contact:Copper Alloy C2680
- 外壳:Shell: Copper Alloy C2680/SPCC

电镀:Finish:

- 端子>Contact: Piated Gold in Mating Area;
Tin On Solder Talls
- 外壳:Shell:
Nickel Plating

深圳市敏连达科技有限公司 Shenzhen Minlianda Technology Co.,Ltd.		品名(ITEM NO)	USB AF 180° DIP 13.7 直脚有卷边		
		料号(PART NO)	MLD-USB AF 180-13.7H		
单位(UNIT): MM	TOLERANCE UNSPECIFIED X.X ± 0.38 X.XX ± 0.20 X.XXX ± 0.10 X' ± 5" X.X' ± 2"	版次(REV): A/0	页次(PAGE):1/1	设计 (DESIGN)	柯南
比例(SCALE) 1:1		模号 (MODEL NO)		审核 (CHECKED)	邱敏
		图号 (DWG NO)		核准(APPROVED)	陈镇
			MLD-2509031032		