







RoHS Compliant



A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME

备注:

1. 材质:

1.1 胶芯: LCP+30%G.F UL94V-0

1.2 端子: C2680; 镍底30-50U" MIN,
接触区域镀金(AU 0.5")焊接区镀金G/F

1.3 外壳: SUS201T=0.30mm; 表面镀镍30-50U" MIN

2. 主要特性:

2.1 额定电流: 3A

2.2 接触阻抗: 40mΩ MAX(初始值)




50mΩ MAX(测试后)

2.6 整体插入力: 5-20N 整体插入力: 5-20N(耐久后)

2.7 耐高温: SMT回流焊(峰值260° ±5°), 塑胶不能有起泡,
融胶等不良, 变色, 翘曲变形在公差范围以内;

2.8 产品须做焊锡测试, 粘锡面积达到95%以上;

3.0 工作温度: -30℃ ~ +85℃



深圳市敏连达科技有限公司 Shenzhen Minlianda Technology Co.,Ltd.		品名(ITEM NO)	USB TYPE C 板上型单排16P SMT 有柱无弹		
		料号(PART NO)	MLD-TYPE-C-3.1-16PIN-L7.35		
单位(UNIT): MM	未注公差 TOLERANCE UNSPECIFIED	版次(REV): A/O	页次(PAGE):1/1	设计 (DESIGN)	柯南
比例(SCALE) 1:1	X.X ± 0.38 X.XX ± 0.20 X.XXX ± 0.10 X" ± 5" X.X" ± 2"	模号 (MODEL NO)	图号 (DWG NO)	审核 (CHECKED)	邱敏
				核准(APPROVED)	陈镇