







RoHS Compliant



RECOMMENDED PCB LAYOUT
(TOLERANCE:±0.05)



NOTES :

1.0. RATING :

- 1.1. VOITAGE :60 VAC (R.M.S.)
- 1.2. NOMINAL CHARACTERISTIC IMPEDANCE: 50 Ohm
- 1.3. APPLICABLE FREQUENCY: DC ~ 6GHz
- 1.4. VSWR: 1.3 MAX. (DC~3GHz), 1.5 MAX. (3~6GHz)
- 1.5. TEMPERATURE : -40°C TO +85°C
- 1.6. APPLIED TO IR SOLDERING PROCESS

2.0. MATERIAL SEE BILL OF MATERIAL :

- 2.1.HOUSING: LCP THERMOPLASTIC,UL94V-0,HALOGEN-FREE
- 2.2.CENTER CONTACT : C5191 COPPER ALLOY.
- 2.3.SHELL CONTACT: C5191 COPPER ALLOY.

深圳市敏连达科技有限公司 Shenzhen Minlianda Technology Co.,Ltd.		品名(ITEM NO)	RF一代板端天线座		
		料号(PART NO)	MLD- IPEX1		
单位(UNIT): MM	未注公差 TOLERANCE UNSPECIFIED X.X ± 0.38 X.XX ± 0.20 X.XXX ± 0.10 X" ± 5" X.X" ± 2"	版次(REV): A/0	页次(PAGE):1/1	设计 (DESIGN)	柯南
比例(SCALE) 1:1		模号 (MODEL NO)	MLD-2509031032	审核 (CHECKED)	邱敏
 		图号 (DWG NO)		核准(APPROVED)	陈镇