


	REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.08.22	




9.PART NO.:


Code: A~Z

Code: A~Z

BOM List:



RECOMMENDED CABLE STRIPPING DIM'S



5	XKS3-PBT01	Outer Ferrule	Copper Alloy	Tin PLATED	1 PC	5K PCS/R
4	XKBF3-PBT232	Outer Conductor	Copper Alloy	Tin PLATED	1 PC	
3	XKTF3-PBGN603	Center Conductor	Copper Alloy	Gold PLATED	1 PC	5K PCS/R
2	XKHF1-PT32-X	Housing	PBT		1 PC	
1	XKC0-PTY01	Secondary Lock	PBT		1 PC	
NO.	P/N	NAME	MATERIAL	FINISH (Contact)	Q' TY	Note

ANGLAR	$\pm 5^\circ$
X.	± 0.50
X.x	± 0.30
X.xx	± 0.15
X.xxx	± 0.05
UNSPECIFIED TOLERANCES	



DESIGN	希 文	VIEW: 	MODEL TYPE: FAKRA Female Connector for RG17
CHECKED		UNIT: mm/in	PART NO.: XK1PLF1S3-NA06-X
APPROVED		SIZE: A4	DWG NO.: X-XK1PLF1S3-NA06-X

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	1/2	A0

A

A

B















B

C

C

D

D

Code List:							
Colde							
	A	B	C	D	E	F	G
Color/RAL-No.	Black/9005	White/9001	Blue/5005	Bordeaux/4004	Green/6002	Brown/8011	Grey/7031
PART NO.	XK1PLF1S3-NA06-A	XK1PLF1S3-NA06-B	XK1PLF1S3-NA06-C	XK1PLF1S3-NA06-D	XK1PLF1S3-NA06-E	XK1PLF1S3-NA06-F	XK1PLF1S3-NA06-G
Colde							
	H	I	K	L	M	N	Z
Color/RAL-No.	Violet/4003	Beige/1001	Curry/1027	Carmine red/3002	Pastel Orange/2003	Pastel Green/6019	Water Blue/5021
PART NO.	XK1PLF1S3-NA06-H	XK1PLF1S3-NA06-I	XK1PLF1S3-NA06-K	XK1PLF1S3-NA06-L	XK1PLF1S3-NA06-M	XK1PLF1S3-NA06-N	XK1PLF1S3-NA06-Z

NOTE: ALL RIGHTS RESERVED,BANNED COPY!

ANGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.15
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	希文	VIEW: 	MODEL TYPE: FAKRA Female Connector for RG174		
CHECKED		UNIT: mm/in	PART NO.: XK1PLF1S3-NA06-X		
APPROVED		SIZE: A4	DWG NO.: X-XK1PLF1S3-NA06-X		
			SCALE	PAGE	REVISION
			N/A	2/2	A0