




RoHS

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.08.22	

- Specifications(规格):
- 1.Impedance(特性阻抗) : 50Ω;
 - 2.Frequency (工作频率) : DC~6GHz;
 - 3.VSWR (电压驻波比) : 1.50 @3GHz;
1.60 @6GHz;
 - 4.Insulation resistance(绝缘阻抗) : ≥100MΩ;
 - 5.Dielectric withstand voltage (介质耐电压) : 800V AC;
 - 6.Mating cycles (耐久性) : ≥25cycles;
 - 7.Retention force latch(保持力) : ≥110N;
 - 8.Temperature range(使用温度): -40℃~+105℃;
 - 9.PART NO.:
XK1PLF1S7-NA06-X
Code: A~Z
 - 10.Housing P/N:
XKHF1-PT32-X
Code: A~Z



BOM List:



5	XKS7-PBT02	Outer Ferrule	Copper Alloy	Tin PLATED	1 PC	5K PCS/R
4	XKBF7-PBT232	Outer Conductor	Copper Alloy	Tin PLATED	1 PC	
3	XKTF7-PBGN604	Center Conductor	Copper Alloy	Gold PLATED	1 PC	5K PCS/R
2	XKHF1-PT32-X	Housing	PBT		1 PC	
1	XKCO-PTY01	Secondary Lock	PBT		1 PC	
NO.	P/N	NAME	MATERIAL	FINISH (Contact)	Q'TY	Note



XKB INDUSTRIAL PRECISION CO.,LIMITED

DESIGN	希文	VIEW:	MODEL TYPE: FAKRA Female Connector for 302
CHECKED		UNIT: mm/in	PART NO.: XK1PLF1S7-NA06-X
APPROVED		SIZE: A4	DWG NO.: X-XK1PLF1S7-NA06-X
			SCALE PAGE REVISION N/A 1/2 A0

1















2

3

4

REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE
A0	N/A		INITIAL RELEASE	2024.08.22

Code List:

Colde							
	A	B	C	D	E	F	G
Color/RAL-No.	Black/9005	White/9001	Blue/5005	Bordeaux/4004	Green/6002	Brown/8011	Grey/7031
PART NO.	XK1PLF1S7-NA06-A	XK1PLF1S7-NA06-B	XK1PLF1S7-NA06-C	XK1PLF1S7-NA06-D	XK1PLF1S7-NA06-E	XK1PLF1S7-NA06-F	XK1PLF1S7-NA06-G
Colde							
	H	I	K	L	M	N	Z
Color/RAL-No.	Violet/4003	Beige/1001	Curry/1027	Carmine red/3002	Pastel Orange/2003	Pastel Green/6019	Water Blue/5021
PART NO.	XK1PLF1S7-NA06-H	XK1PLF1S7-NA06-I	XK1PLF1S7-NA06-K	XK1PLF1S7-NA06-L	XK1PLF1S7-NA06-M	XK1PLF1S7-NA06-N	XK1PLF1S7-NA06-Z

NOTE: ALL RIGHTS RESERVED,BANNED COPY!

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn

ANGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.15
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	希文	VIEW: 	MODEL TYPE: FAKRA Female Connector for 302
CHECKED		UNIT: mm/in	PART NO.: XK1PLF1S7-NA06-X
APPROVED		SIZE: A4	DWG NO.: X-XK1PLF1S7-NA06-X
			SCALE PAGE REVISION
			N/A 2/2 A0

XKB INDUSTRIAL PRECISION CO.,LIMITED

1

2

3

4