

RoHS		2	3	4	5	6	7	8	9																																																																																
								<table border="1"><thead><tr><th>序号 (NO.)</th><th>品名 (Name)</th><th>材质 (Material)</th></tr></thead><tbody><tr><td>①</td><td>2.00 F型卧式2代WTB胶芯 2.00 Pitch R/A Wire To Board Housing(H=5.2)</td><td>LCP UL94V-0 本色 Natural</td></tr><tr><td>②</td><td>2.00 F型卧式2代WTB端子 2.00 Pitch R/A Wire To Board Terminal(H=5.2)</td><td>铜合金/表面镀锡 Copper Alloy/ Tin Plating</td></tr><tr><td>③</td><td>2.00 F型卧式WTB焊片 2.00 Pitch R/A Wire To Board Fitting Nail(H=5.6)</td><td>铜合金/表面镀锡 Copper Alloy/ Tin Plating</td></tr></tbody></table>		序号 (NO.)	品名 (Name)	材质 (Material)	①	2.00 F型卧式2代WTB胶芯 2.00 Pitch R/A Wire To Board Housing(H=5.2)	LCP UL94V-0 本色 Natural	②	2.00 F型卧式2代WTB端子 2.00 Pitch R/A Wire To Board Terminal(H=5.2)	铜合金/表面镀锡 Copper Alloy/ Tin Plating	③	2.00 F型卧式WTB焊片 2.00 Pitch R/A Wire To Board Fitting Nail(H=5.6)	铜合金/表面镀锡 Copper Alloy/ Tin Plating																																																																				
序号 (NO.)	品名 (Name)	材质 (Material)																																																																																							
①	2.00 F型卧式2代WTB胶芯 2.00 Pitch R/A Wire To Board Housing(H=5.2)	LCP UL94V-0 本色 Natural																																																																																							
②	2.00 F型卧式2代WTB端子 2.00 Pitch R/A Wire To Board Terminal(H=5.2)	铜合金/表面镀锡 Copper Alloy/ Tin Plating																																																																																							
③	2.00 F型卧式WTB焊片 2.00 Pitch R/A Wire To Board Fitting Nail(H=5.6)	铜合金/表面镀锡 Copper Alloy/ Tin Plating																																																																																							
		2 PIN 结构样式 (Structural style) 3 PIN 结构样式 (Structural style)						<table border="1"><thead><tr><th>CKT</th><th>DIM A</th><th>DIM B</th><th>DIM C</th></tr></thead><tbody><tr><td>2</td><td>2.00</td><td>4.90</td><td>8.00</td></tr><tr><td>3</td><td>4.00</td><td>6.90</td><td>10.00</td></tr><tr><td>4</td><td>6.00</td><td>8.90</td><td>12.00</td></tr><tr><td>5</td><td>8.00</td><td>10.90</td><td>14.00</td></tr><tr><td>6</td><td>10.00</td><td>12.90</td><td>16.00</td></tr><tr><td>7</td><td>12.00</td><td>14.90</td><td>18.00</td></tr><tr><td>8</td><td>14.00</td><td>16.90</td><td>20.00</td></tr><tr><td>9</td><td>16.00</td><td>18.90</td><td>22.00</td></tr><tr><td>10</td><td>18.00</td><td>20.90</td><td>24.00</td></tr><tr><td>11</td><td>20.00</td><td>22.90</td><td>26.00</td></tr><tr><td>12</td><td>22.00</td><td>24.90</td><td>28.00</td></tr><tr><td>13</td><td>24.00</td><td>26.90</td><td>30.00</td></tr><tr><td>14</td><td>26.00</td><td>28.90</td><td>32.00</td></tr><tr><td>15</td><td>28.00</td><td>30.90</td><td>34.00</td></tr><tr><td>16</td><td>30.00</td><td>32.90</td><td>36.00</td></tr><tr><td>17</td><td>32.00</td><td>34.90</td><td>38.00</td></tr><tr><td>18</td><td>34.00</td><td>36.90</td><td>40.00</td></tr><tr><td>19</td><td>36.00</td><td>38.90</td><td>42.00</td></tr><tr><td>20</td><td>38.00</td><td>40.90</td><td>44.00</td></tr></tbody></table>		CKT	DIM A	DIM B	DIM C	2	2.00	4.90	8.00	3	4.00	6.90	10.00	4	6.00	8.90	12.00	5	8.00	10.90	14.00	6	10.00	12.90	16.00	7	12.00	14.90	18.00	8	14.00	16.90	20.00	9	16.00	18.90	22.00	10	18.00	20.90	24.00	11	20.00	22.90	26.00	12	22.00	24.90	28.00	13	24.00	26.90	30.00	14	26.00	28.90	32.00	15	28.00	30.90	34.00	16	30.00	32.90	36.00	17	32.00	34.90	38.00	18	34.00	36.90	40.00	19	36.00	38.90	42.00	20	38.00	40.90	44.00
CKT	DIM A	DIM B	DIM C																																																																																						
2	2.00	4.90	8.00																																																																																						
3	4.00	6.90	10.00																																																																																						
4	6.00	8.90	12.00																																																																																						
5	8.00	10.90	14.00																																																																																						
6	10.00	12.90	16.00																																																																																						
7	12.00	14.90	18.00																																																																																						
8	14.00	16.90	20.00																																																																																						
9	16.00	18.90	22.00																																																																																						
10	18.00	20.90	24.00																																																																																						
11	20.00	22.90	26.00																																																																																						
12	22.00	24.90	28.00																																																																																						
13	24.00	26.90	30.00																																																																																						
14	26.00	28.90	32.00																																																																																						
15	28.00	30.90	34.00																																																																																						
16	30.00	32.90	36.00																																																																																						
17	32.00	34.90	38.00																																																																																						
18	34.00	36.90	40.00																																																																																						
19	36.00	38.90	42.00																																																																																						
20	38.00	40.90	44.00																																																																																						
		<table border="1"><thead><tr><th colspan="2">OPERATION</th><th rowspan="2">DRAW</th><th rowspan="2">SCALE</th><th rowspan="2">FIT</th><th colspan="2" rowspan="3">深圳市连盛精密连接器有限公司</th></tr><tr><th>X.X</th><th>±0.30</th></tr></thead><tbody><tr><td>X.XX</td><td>±0.20</td><td>CHECK</td><td>UNIT</td><td>mm</td><td>PART NO.</td><td>1130300236</td></tr><tr><td>X.XXX</td><td>±0.10</td><td rowspan="2">APPROVE</td><td>SIZE</td><td>A4</td><td>TITLE:</td><td>HY-AWR</td></tr><tr><td>Angle</td><td>±3°</td><td>SHEET</td><td>1/1</td><td></td><td></td></tr><tr><td>DIM</td><td>TOL</td><td>PROJ.</td><td>◆</td><td></td><td></td><td></td></tr></tbody></table>						OPERATION		DRAW	SCALE	FIT	深圳市连盛精密连接器有限公司		X.X	±0.30	X.XX	±0.20	CHECK	UNIT	mm	PART NO.	1130300236	X.XXX	±0.10	APPROVE	SIZE	A4	TITLE:	HY-AWR	Angle	±3°	SHEET	1/1			DIM	TOL	PROJ.	◆																																																	
OPERATION		DRAW	SCALE	FIT	深圳市连盛精密连接器有限公司																																																																																				
X.X	±0.30																																																																																								
X.XX	±0.20	CHECK	UNIT	mm			PART NO.	1130300236																																																																																	
X.XXX	±0.10	APPROVE	SIZE	A4	TITLE:	HY-AWR																																																																																			
Angle	±3°		SHEET	1/1																																																																																					
DIM	TOL	PROJ.	◆																																																																																						
A0		2012.04.18	NEW DRAWING	CHANGE																																																																																					
REV		DATE	MODIFICATION DESCRIPTION	CHANGE																																																																																					

[illegible]

A

F

G

B

C

D

E

F

G

1

2

3

4

5

6

7

8

9

RoHS

0.5±0.03(SQ)

2.00±0.15(PITCH)

①

②

③

DIM A ±0.2
DIM B ±0.15
DIM C ±0.2

2 PIN 结构样式
(Structural style)

3 PIN 结构样式
(Structural style)

2.60±0.2

6.65

1.2

5.2

△0.13

适用线路板(PCB LAYOUT)

DIM A ±0.1
2±0.05

1.2±0.1

3.80

3.85±0.1

3.70

1.20

2.2

CONN.

0.75

序号(No.)

品名(Name)

材质(Material)

①

2.00 F型卧式2代WTB胶芯
2.00 Pitch R/A Wire To Board Housing(H=5.2)

LCP UL94V-0
本色 Natural

②

2.00 F型卧式2代WTB端子
2.00 Pitch R/A Wire To Board Terminal(H=5.2)

铜合金/表面镀锡
Copper Alloy/
Tin Plating

③

2.00 F型卧式WTB焊片
2.00 Pitch R/A Wire To Board Fitting Nail(H=5.6)

铜合金/表面镀锡
Copper Alloy/
Tin Plating

技术指标(Technical Index):

1.温度范围(Temperature range):-40℃~+105℃.

2.额定电压(Rated voltage):200V, AC.

3.额定电流(Rated Current):2A AC/DC

4.接触电阻(Contact resistance)≤20mΩ

5.绝缘电阻(Insulation resistance)≥1000MΩ.

6.产品料号(Product material No.):

CTK

DIM A

DIM B

DIM C

2

2.00

4.90

8.00

3

4.00

6.90

10.00

4

6.00

8.90

12.00

5

8.00

10.90

14.00

6

10.00

12.90

16.00

7

12.00

14.90

18.00

8

14.00

16.90

20.00

9

16.00

18.90

22.00

10

18.00

20.90

24.00

11

20.00

22.90

26.00

12

22.00

24.90

28.00

13

24.00

26.90

30.00

14

26.00

28.90

32.00

15

28.00

30.90

34.00

16

30.00

32.90

36.00

17

32.00

34.90

38.00

18

34.00

36.90

40.00

19

36.00

38.90

42.00

20

38.00

40.90

44.00

OPERATION

X.X

±0.30

DRAW

SCALE

FIT

深圳市连盛精密连接器有限公司

X.XX

±0.20

CHECK

UNIT

mm

A0

2012.04.18

NEW DRAWING

SHEET

1/1

PART NO.

1130300236

REV

DATE

MODIFICATION DESCRIPTION

CHANGE

PROJ.

TITLE:

HY-AWR

- [illegible]

RoHS		2	3	4	5	6	7	8	9												
								<table><tr><th>序号 (NO.)</th><th>品名 (Name)</th><th>材质 (Material)</th></tr><tr><td>①</td><td>2.00 F型卧式2代WTB胶芯 2.00 Pitch R/A Wire To Board Housing(H=5.2)</td><td>LCP UL94V-0 本色 Natural</td></tr><tr><td>②</td><td>2.00 F型卧式2代WTB端子 2.00 Pitch R/A Wire To Board Terminal(H=5.2)</td><td>铜合金/表面镀锡 Copper Alloy/ Tin Plating</td></tr><tr><td>③</td><td>2.00 F型卧式WTB焊片 2.00 Pitch R/A Wire To Board Fitting Nail(H=5.6)</td><td>铜合金/表面镀锡 Copper Alloy/ Tin Plating</td></tr></table>		序号 (NO.)	品名 (Name)	材质 (Material)	①	2.00 F型卧式2代WTB胶芯 2.00 Pitch R/A Wire To Board Housing(H=5.2)	LCP UL94V-0 本色 Natural	②	2.00 F型卧式2代WTB端子 2.00 Pitch R/A Wire To Board Terminal(H=5.2)	铜合金/表面镀锡 Copper Alloy/ Tin Plating	③	2.00 F型卧式WTB焊片 2.00 Pitch R/A Wire To Board Fitting Nail(H=5.6)	铜合金/表面镀锡 Copper Alloy/ Tin Plating
序号 (NO.)	品名 (Name)	材质 (Material)																			
①	2.00 F型卧式2代WTB胶芯 2.00 Pitch R/A Wire To Board Housing(H=5.2)	LCP UL94V-0 本色 Natural																			
②	2.00 F型卧式2代WTB端子 2.00 Pitch R/A Wire To Board Terminal(H=5.2)	铜合金/表面镀锡 Copper Alloy/ Tin Plating																			
③	2.00 F型卧式WTB焊片 2.00 Pitch R/A Wire To Board Fitting Nail(H=5.6)	铜合金/表面镀锡 Copper Alloy/ Tin Plating																			

[illegible]