

A0

REV

DATE

MODIFICATION DESCRIPTION

CHANGE

NEW DRAWING

OPERATION

X.X ±0.30

X.XX ±0.20

X.XXX ±0.10

Angle ±3°

DIM TOL

DRAW

CHECK

APPROVE

SCALE

FIT

UNIT mm

SHEET A4

PROJECT SHEET 1/1

PART NO.

TITLE:

1130300240

HY-NAWR

RoHS

1

2

3

4

5

6

7

8

9

0.5±0.03(SQ)

2.00±0.15(PITCH)

①

②

③

2 PIN 结构样式
(Structural style)

3 PIN 结构样式
(Structural style)

适用线路板(PCB LAYOUT)

技术指标(Technical Index):
1.温度范围(Temperature range):-40°C~+105°C.
2.额定电压(Rated voltage):200V, AC.
3.额定电流(Rated Current):2A AC/DC
4.接触电阻(Contact resistance):≤20mΩ
5.绝缘电阻(Insulation resistance):≥1000MΩ.
6.产品料号(Product material No.):

CTK DIM A DIM B DIM C

2 2.00 4.90 8.00

3 4.00 6.90 10.00

4 6.00 8.90 12.00

5 8.00 10.90 14.00

6 10.00 12.90 16.00

7 12.00 14.90 18.00

8 14.00 16.90 20.00

9 16.00 18.90 22.00

10 18.00 20.90 24.00

11 20.00 22.90 26.00

12 22.00 24.90 28.00

13 24.00 26.90 30.00

14 26.00 28.90 32.00

15 28.00 30.90 34.00

16 30.00 32.90 36.00

17 32.00 34.90 38.00

18 34.00 36.90 40.00

19 36.00 38.90 42.00

20 38.00 40.90 44.00

[illegible][illegible]

- A

F

G

B

C

D

E

RoHS

0.5±0.03(SQ)

2.00±0.15(PITCH)

①

6.65

1.2

5.2

△0.13

③

2.60±0.2

②

DIMA±0.2
DIMB±0.15
DIMC±0.2

2 PIN 结构样式
(Structural style)

3 PIN 结构样式
(Structural style)

适用线路板(PCB LAYOUT)

DIMA±0.1
2±0.05

1.2±0.1

3.80

3.85±0.1

3.70

1.20

2.2

CONN.

0.75

序号(No.)

品名(Name)

材质(Material)

①

2.00 F型卧式2代WTB胶芯
2.00 Pitch R/A Wire To Board Housing(H=5.2)

LCP UL94V-0
本色 Natural

②

2.00 F型卧式2代WTB端子
2.00 Pitch R/A Wire To Board Terminal(H=5.2)

铜合金/表面镀锡
Copper Alloy/
Tin Plating

③

2.00 F型卧式WTB焊片
2.00 Pitch R/A Wire To Board Fitting Nail(H=5.6)

铜合金/表面镀锡
Copper Alloy/
Tin Plating

技术指标(Technical Index):
1.温度范围(Temperature range):-40℃~+105℃.
2.额定电压(Rated voltage):200V, AC.
3.额定电流(Rated Current):2A AC/DC
4.接触电阻(Contact resistance)≤20mΩ
5.绝缘电阻(Insulation resistance)≥1000MΩ.
6.产品料号(Product material No.):

CKT

DIM A

DIM B

DIM C

2

2.00

4.90

8.00

3

4.00

6.90

10.00

4

6.00

8.90

12.00

5

8.00

10.90

14.00

6

10.00

12.90

16.00

7

12.00

14.90

18.00

8

14.00

16.90

20.00

9

16.00

18.90

22.00

10

18.00

20.90

24.00

11

20.00

22.90

26.00

12

22.00

24.90

28.00

13

24.00

26.90

30.00

14

26.00

28.90

32.00

15

28.00

30.90

34.00

16

30.00

32.90

36.00

17

32.00

34.90

38.00

18

34.00

36.90

40.00

19

36.00

38.90

42.00

20

38.00

40.90

44.00

OPERATION

X.X ±0.30

X.XX ±0.20

X.XXX ±0.10

Angle ±3°

DIM TOL

DRAW

CHECK

APPROVE

SCALE

FIT

UNITmm

SHEETA4

SHEETA4

PROJ.

深圳市连盛精密连接器有限公司

PART NO.

TITLE:

1130300240

HY-AWR

1

2

3

4

5

6

7

8

9

[illegible][illegible]