

	2	3	4	5	6	7	8	9																																																																																	
G	RoHS																																																																																								
F																																																																																									
E			技术指标(Technical Index): 1. 温度范围(Temperature range): -40° C~+ 105° C. 2. 额定电压(Rated voltage): 200V, AC. 3. 额定电流(Rated Current):2A AC/DC 4. 接触电阻(Contact resistance): ≤20mΩ 5. 绝缘电阻(Insulation resistance): ≥1000MΩ. 6. 产品料号(Product material No.):																																																																																						
D																																																																																									
C			<table border="1"><thead><tr><th>CKT</th><th>DIM A</th><th>DIM B</th><th>DIM C</th></tr></thead><tbody><tr><td>2</td><td>2.00</td><td>4.90</td><td>8.00</td></tr><tr><td>3</td><td>4.00</td><td>6.90</td><td>10.00</td></tr><tr><td>4</td><td>6.00</td><td>8.90</td><td>12.00</td></tr><tr><td>5</td><td>8.00</td><td>10.90</td><td>14.00</td></tr><tr><td>6</td><td>10.00</td><td>12.90</td><td>16.00</td></tr><tr><td>7</td><td>12.00</td><td>14.90</td><td>18.00</td></tr><tr><td>8</td><td>14.00</td><td>16.90</td><td>20.00</td></tr><tr><td>9</td><td>16.00</td><td>18.90</td><td>22.00</td></tr><tr><td>10</td><td>18.00</td><td>20.90</td><td>24.00</td></tr><tr><td>11</td><td>20.00</td><td>22.90</td><td>26.00</td></tr><tr><td>12</td><td>22.00</td><td>24.90</td><td>28.00</td></tr><tr><td>13</td><td>24.00</td><td>26.90</td><td>30.00</td></tr><tr><td>14</td><td>26.00</td><td>28.90</td><td>32.00</td></tr><tr><td>15</td><td>28.00</td><td>30.90</td><td>34.00</td></tr><tr><td>16</td><td>30.00</td><td>32.90</td><td>36.00</td></tr><tr><td>17</td><td>32.00</td><td>34.90</td><td>38.00</td></tr><tr><td>18</td><td>34.00</td><td>36.90</td><td>40.00</td></tr><tr><td>19</td><td>36.00</td><td>38.90</td><td>42.00</td></tr><tr><td>20</td><td>38.00</td><td>40.90</td><td>44.00</td></tr></tbody></table>						CKT	DIM A	DIM B	DIM C	2	2.00	4.90	8.00	3	4.00	6.90	10.00	4	6.00	8.90	12.00	5	8.00	10.90	14.00	6	10.00	12.90	16.00	7	12.00	14.90	18.00	8	14.00	16.90	20.00	9	16.00	18.90	22.00	10	18.00	20.90	24.00	11	20.00	22.90	26.00	12	22.00	24.90	28.00	13	24.00	26.90	30.00	14	26.00	28.90	32.00	15	28.00	30.90	34.00	16	30.00	32.90	36.00	17	32.00	34.90	38.00	18	34.00	36.90	40.00	19	36.00	38.90	42.00	20	38.00	40.90	44.00	
CKT	DIM A	DIM B	DIM C																																																																																						
2	2.00	4.90	8.00																																																																																						
3	4.00	6.90	10.00																																																																																						
4	6.00	8.90	12.00																																																																																						
5	8.00	10.90	14.00																																																																																						
6	10.00	12.90	16.00																																																																																						
7	12.00	14.90	18.00																																																																																						
8	14.00	16.90	20.00																																																																																						
9	16.00	18.90	22.00																																																																																						
10	18.00	20.90	24.00																																																																																						
11	20.00	22.90	26.00																																																																																						
12	22.00	24.90	28.00																																																																																						
13	24.00	26.90	30.00																																																																																						
14	26.00	28.90	32.00																																																																																						
15	28.00	30.90	34.00																																																																																						
16	30.00	32.90	36.00																																																																																						
17	32.00	34.90	38.00																																																																																						
18	34.00	36.90	40.00																																																																																						
19	36.00	38.90	42.00																																																																																						
20	38.00	40.90	44.00																																																																																						
B			<table border="1"><thead><tr><th>CT</th><th>DATE</th><th>DESCRIPTION</th><th>CHANGE</th><th>OPERATION</th><th>DRAW</th><th>SCALE</th><th>FIT</th><th colspan="2">深圳市连盛精密连接器有限公司</th></tr></thead><tbody><tr><td>A0</td><td>2012.04.18</td><td>NEW DRAWING</td><td></td><td>X.X ±0.30</td><td rowspan="3">CHECK</td><td>UNIT</td><td>mm</td><td rowspan="2">PART NO.</td><td rowspan="2">1130300131</td></tr><tr><td></td><td></td><td></td><td></td><td>X.XX ±0.20</td><td>SIZE</td><td>A4</td></tr><tr><td></td><td></td><td></td><td></td><td>X.XXX ±0.10</td><td>SHEET</td><td>1/1</td><td>TITLE:</td><td>HY-NAWR</td></tr><tr><td></td><td>REV</td><td>DATE</td><td>MODIFICATION DESCRIPTION</td><td>CHANGE</td><td>ANGLE ±3'</td><td>PROJ.</td><td></td><td></td><td></td></tr><tr><td></td><td></td><td></td><td></td><td></td><td>DIM TOL</td><td></td><td></td><td></td><td></td></tr></tbody></table>						CT	DATE	DESCRIPTION	CHANGE	OPERATION	DRAW	SCALE	FIT	深圳市连盛精密连接器有限公司		A0	2012.04.18	NEW DRAWING		X.X ±0.30	CHECK	UNIT	mm	PART NO.	1130300131					X.XX ±0.20	SIZE	A4					X.XXX ±0.10	SHEET	1/1	TITLE:	HY-NAWR		REV	DATE	MODIFICATION DESCRIPTION	CHANGE	ANGLE ±3'	PROJ.									DIM TOL																													
CT	DATE	DESCRIPTION	CHANGE	OPERATION	DRAW	SCALE	FIT	深圳市连盛精密连接器有限公司																																																																																	
A0	2012.04.18	NEW DRAWING		X.X ±0.30	CHECK	UNIT	mm	PART NO.	1130300131																																																																																
				X.XX ±0.20		SIZE	A4																																																																																		
				X.XXX ±0.10		SHEET	1/1	TITLE:	HY-NAWR																																																																																
	REV	DATE	MODIFICATION DESCRIPTION	CHANGE	ANGLE ±3'	PROJ.																																																																																			
					DIM TOL																																																																																				
A	1	2	3	4	5	6	7	8	9																																																																																

[illegible][illegible]

- [illegible]

[illegible][illegible]