





REV.	REVISION DESCRIPTION	DATE	APPD

NOTES


OF max.	动作力 最大	150g
RF min.	回复力 最小	30g
PT max.	预行程 最大	3mm
MD max.	差 程 最大	1mm
OP	动作位置	15.5±1mm
FP max.	自由位置 最大	19mm

Rated Voltage	额定电压	125/250VAC
Rated Current	额定电流	16A
Rated Frequency	额定频率	50/60Hz
Contact Resistance	接触电阻	30 mΩ max.
Insulation Resistance	绝缘电阻	100 MΩ min.at 500VDC
Dielectrics Strength	介电强度	Between terminals: AC 1000V/min 50/60Hz for 1 min Terminals and Groud: AC 1500V/min 50/60Hz for 1 min
Ambient Air Temperature	环境温度	25T85 (-25°C to 85°C)
Ambient Humidity	相对湿度	85%(5 to 35)
Electrical Life	电气寿命	1E4 10,000 times min.
Mechanical Life	机械寿命	1E6 1,000,000 times min.



CONTACT FORM 接触形式

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO., LTD	
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME:	TITLE:
.XX: ± 0.15	.X° : ± 2.0°	DL-KW7-1-G07	MICRO SWITCH 微动开关
.XXX: ± 0.01	.XX° : ± 1.0°	DR: Chen Quan Long	DATE:19/08/01
FINISH:		CHKD: Wu Hui	DATE:19/08/01
DRAWING NO:		APPD:Ren An De	DATE:19/08/01
		SCALE: N/A	PAGE: 1/1
		UNITS: mm	REV.: A



NOTES

OF max.	动作力 最大	150g
RF min.	回复力 最小	30g
PT max.	预行程 最大	3mm
MD max.	差程 最大	1mm
OP	动作位置	21±1mm
FP max.	自由位置 最大	25mm
Rated Voltage	额定电压	125/250VAC
Rated Current	额定电流	16A
Rated Frequency	额定频率	50/60Hz
Contact Resistance	接触电阻	30 mΩ max.
Insulation Resistance	绝缘电阻	100 MΩ min.at 500VDC
Dielectrics Strength	介电强度	Between terminals: AC 1000V/min 50/60Hz for 1 min Terminals and Groud: AC 1500V/min 50/60Hz for 1 min
Ambient Air Temperature	环境温度	25T85 (-25°C to 85°C)
Ambient Humidity	相对湿度	85%(5 to 35)
Electrical Life	电气寿命	1E4 10,000 times min.
Mechanical Life	机械寿命	1E6 1,000,000 times min.

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO ., LTD			
. X: ± 0.25	X° : ± 3.0°	PRODUCT NAME:		TITLE:	
. XX: ± 0.15	. X° : ± 2.0°	DL-KW7-2-G07		MICRO SWITCH 微动开关	
. XXX: ± 0.01	. XX° : ± 1.0°	DR: Chen Quan Long	DATE:19/08/01	PART NO:	
FINISH:		CHKD: Wu Hui	DATE:19/08/01	SCALE: N/A	PAGE: 1/1
DRAWING NO:		APPD:Ren An De	DATE:19/08/01	UNITS: mm	REV. : A