

[illegible][illegible][illegible]

- [illegible]

RoHS		2	3	4	5	6	7	8	9																																																																																
								<table><tr><th>序号 (NO.)</th><th>品名 (Name)</th><th>材质 (Material)</th></tr><tr><td>①</td><td>2.00 F型卧式2代WTB胶芯 2.00 Pitch R/A Wire To Board Housing(H=5.2)</td><td>LCP UL94V-0 本色 Natural</td></tr><tr><td>②</td><td>2.00 F型卧式2代WTB端子 2.00 Pitch R/A Wire To Board Terminal(H=5.2)</td><td>铜合金/表面镀锡 Copper Alloy/ Tin Plating</td></tr><tr><td>③</td><td>2.00 F型卧式WTB焊片 2.00 Pitch R/A Wire To Board Fitting Nail(H=5.6)</td><td>铜合金/表面镀锡 Copper Alloy/ Tin Plating</td></tr></table>		序号 (NO.)	品名 (Name)	材质 (Material)	①	2.00 F型卧式2代WTB胶芯 2.00 Pitch R/A Wire To Board Housing(H=5.2)	LCP UL94V-0 本色 Natural	②	2.00 F型卧式2代WTB端子 2.00 Pitch R/A Wire To Board Terminal(H=5.2)	铜合金/表面镀锡 Copper Alloy/ Tin Plating	③	2.00 F型卧式WTB焊片 2.00 Pitch R/A Wire To Board Fitting Nail(H=5.6)	铜合金/表面镀锡 Copper Alloy/ Tin Plating																																																																				
序号 (NO.)	品名 (Name)	材质 (Material)																																																																																							
①	2.00 F型卧式2代WTB胶芯 2.00 Pitch R/A Wire To Board Housing(H=5.2)	LCP UL94V-0 本色 Natural																																																																																							
②	2.00 F型卧式2代WTB端子 2.00 Pitch R/A Wire To Board Terminal(H=5.2)	铜合金/表面镀锡 Copper Alloy/ Tin Plating																																																																																							
③	2.00 F型卧式WTB焊片 2.00 Pitch R/A Wire To Board Fitting Nail(H=5.6)	铜合金/表面镀锡 Copper Alloy/ Tin Plating																																																																																							
								<table><tr><th>CKT</th><th>DIM A</th><th>DIM B</th><th>DIM C</th></tr><tr><td>2</td><td>2.00</td><td>4.90</td><td>8.00</td></tr><tr><td>3</td><td>4.00</td><td>6.90</td><td>10.00</td></tr><tr><td>4</td><td>6.00</td><td>8.90</td><td>12.00</td></tr><tr><td>5</td><td>8.00</td><td>10.90</td><td>14.00</td></tr><tr><td>6</td><td>10.00</td><td>12.90</td><td>16.00</td></tr><tr><td>7</td><td>12.00</td><td>14.90</td><td>18.00</td></tr><tr><td>8</td><td>14.00</td><td>16.90</td><td>20.00</td></tr><tr><td>9</td><td>16.00</td><td>18.90</td><td>22.00</td></tr><tr><td>10</td><td>18.00</td><td>20.90</td><td>24.00</td></tr><tr><td>11</td><td>20.00</td><td>22.90</td><td>26.00</td></tr><tr><td>12</td><td>22.00</td><td>24.90</td><td>28.00</td></tr><tr><td>13</td><td>24.00</td><td>26.90</td><td>30.00</td></tr><tr><td>14</td><td>26.00</td><td>28.90</td><td>32.00</td></tr><tr><td>15</td><td>28.00</td><td>30.90</td><td>34.00</td></tr><tr><td>16</td><td>30.00</td><td>32.90</td><td>36.00</td></tr><tr><td>17</td><td>32.00</td><td>34.90</td><td>38.00</td></tr><tr><td>18</td><td>34.00</td><td>36.90</td><td>40.00</td></tr><tr><td>19</td><td>36.00</td><td>38.90</td><td>42.00</td></tr><tr><td>20</td><td>38.00</td><td>40.90</td><td>44.00</td></tr></table>		CKT	DIM A	DIM B	DIM C	2	2.00	4.90	8.00	3	4.00	6.90	10.00	4	6.00	8.90	12.00	5	8.00	10.90	14.00	6	10.00	12.90	16.00	7	12.00	14.90	18.00	8	14.00	16.90	20.00	9	16.00	18.90	22.00	10	18.00	20.90	24.00	11	20.00	22.90	26.00	12	22.00	24.90	28.00	13	24.00	26.90	30.00	14	26.00	28.90	32.00	15	28.00	30.90	34.00	16	30.00	32.90	36.00	17	32.00	34.90	38.00	18	34.00	36.90	40.00	19	36.00	38.90	42.00	20	38.00	40.90	44.00
CKT	DIM A	DIM B	DIM C																																																																																						
2	2.00	4.90	8.00																																																																																						
3	4.00	6.90	10.00																																																																																						
4	6.00	8.90	12.00																																																																																						
5	8.00	10.90	14.00																																																																																						
6	10.00	12.90	16.00																																																																																						
7	12.00	14.90	18.00																																																																																						
8	14.00	16.90	20.00																																																																																						
9	16.00	18.90	22.00																																																																																						
10	18.00	20.90	24.00																																																																																						
11	20.00	22.90	26.00																																																																																						
12	22.00	24.90	28.00																																																																																						
13	24.00	26.90	30.00																																																																																						
14	26.00	28.90	32.00																																																																																						
15	28.00	30.90	34.00																																																																																						
16	30.00	32.90	36.00																																																																																						
17	32.00	34.90	38.00																																																																																						
18	34.00	36.90	40.00																																																																																						
19	36.00	38.90	42.00																																																																																						
20	38.00	40.90	44.00																																																																																						
								<table><tr><th colspan="2">OPERATION</th><th rowspan="2">DRAW</th><th rowspan="2">SCALE</th><th rowspan="2">FIT</th><th colspan="2" rowspan="5">深圳市连盛精密连接器有限公司</th></tr><tr><th>X.X</th><th>±0.30</th></tr><tr><td>X.XX</td><td>±0.20</td><td>CHECK</td><td>UNIT</td><td>mm</td></tr><tr><td>X.XXX</td><td>±0.10</td><td rowspan="2">APPROVE</td><td>SIZE</td><td>A4</td></tr><tr><td>Angle</td><td>±3°</td><td>SHEET</td><td>1/1</td></tr><tr><td>DIM</td><td>TOL</td><td>PROJ.</td><td colspan="2">PART NO. 1130300237</td></tr><tr><td colspan="3"></td><td colspan="2">TITLE: HY-NAWR</td></tr></table>		OPERATION		DRAW	SCALE	FIT	深圳市连盛精密连接器有限公司		X.X	±0.30	X.XX	±0.20	CHECK	UNIT	mm	X.XXX	±0.10	APPROVE	SIZE	A4	Angle	±3°	SHEET	1/1	DIM	TOL	PROJ.	PART NO. 1130300237					TITLE: HY-NAWR																																																
OPERATION		DRAW	SCALE	FIT	深圳市连盛精密连接器有限公司																																																																																				
X.X	±0.30																																																																																								
X.XX	±0.20	CHECK	UNIT	mm																																																																																					
X.XXX	±0.10	APPROVE	SIZE	A4																																																																																					
Angle	±3°		SHEET	1/1																																																																																					
DIM	TOL	PROJ.	PART NO. 1130300237																																																																																						
			TITLE: HY-NAWR																																																																																						
A0 2012.04.18 NEW DRAWING		CHANGE																																																																																							
REV	DATE	MODIFICATION DESCRIPTION	CHANGE																																																																																						

[illegible]