






RoHS

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.08.12	

- Specifications(规格):
- 1.Impedance(特性阻抗) : 50Ω;
 - 2.Frequency (工作频率) : DC~6GHz;
 - 3.VSWR (电压驻波比) : 1.50@3GHz;
1.60@6GHz;
 - 4.Insulation resistance(绝缘阻抗) : ≥100MΩ;
 - 5.Dielectric withstand voltage (介质耐电压) : 800V AC;
 - 6.Mating cycles (耐久性) : ≥5 cycles ;
 - 7.Retention force latch(保持力) : ≥110N;
 - 8.Temperature range(使用温度) : -40℃~+105℃;
 - 9.Waterproof Rating(防水等级) : IP67;
 - 10.PART NO.:
XK1PLM1S3-WA06-X
Code: A~Z
 - 11.Housing P/N:
XKHM1-PT12-X
Code: A~Z




3D View



RECOMMENDED CABLE STRIPPING DIM'S

BOM List:



ANGLAR	±5°
X.	±0.50
X.x	±0.30
X.xx	±0.15
X.xxx	±0.05
UNSPECIFIED TOLERANCES	

8	XKC1-PTY13	Secondary Lock	PBT		1 PC	
7	XKC0-PTB12	Cover	PBT		1 PC	
6	XKMY-RB03	Waterproof ring	Silicon Rubber		1 PC	
5	XKD-PTB13	Sheath	PBT		1 PC	
4	XKS7-PBT02	Outer Ferrule	Copper Alloy	Tin PLATED	1 PC	5K PCS/R
3	XKBM7-PBT237	Outer Conductor	Copper Alloy	Tin PLATED	1 PC	
2	XKTM7-PBGN602	Center Conductor	Copper Alloy	Gold PLATED	1 PC	5K PCS/R
1	XKHM1-PT12-X	Housing	PBT		1 PC	
NO.	P/N	NAME	MATERIAL	FINISH (Contact)	Q' TY	Note
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						



DESIGN	希文	VIEW:	MODEL TYPE: FAKRA Male Connector for 302,IP67
CHECKED		UNIT: mm/in	PART NO.: XK1PLM1S7-WA16-X
APPROVED		SIZE: A4	DWG NO.: X-XK1PLM1S7-WA16-X
XKB INDUSTRIAL PRECISION CO.,LIMITED			SCALE PAGE REVISION N/A 1/2 A0

1















2

3

4

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.08.12	

Code List:

Colde							
	A	B	C	D	E	F	G
Color/RAL-No.	Black/9005	White/9001	Blue/5005	Bordeaux/4004	Green/6002	Brown/8011	Grey/7031
PART NO.	XK1PLM1S7-WA16-A	XK1PLM1S7-WA16-B	XK1PLM1S7-WA16-C	XK1PLM1S7-WA16-D	XK1PLM1S7-WA16-E	XK1PLM1S7-WA16-F	XK1PLM1S7-WA16-G
Colde							
	H	I	K	L	M	N	Z
Color/RAL-No.	Violet/4003	Beige/1001	Curry/1027	Carmine red/3002	Pastel Orange/2003	Pastel Green/6019	Water Blue/5021
PART NO.	XK1PLM1S7-WA16-H	XK1PLM1S7-WA16-I	XK1PLM1S7-WA16-K	XK1PLM1S7-WA16-L	XK1PLM1S7-WA16-M	XK1PLM1S7-WA16-N	XK1PLM1S7-WA16-Z

NOTE: ALL RIGHTS RESERVED,BANNED COPY!

ANGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.15
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	希文	VIEW: 	MODEL TYPE: FAKRA Male Connector for 302,IP67
CHECKED		UNIT: mm/in	PART NO.: XK1PLM1S7-WA16-X
APPROVED		SIZE: A4	DWG NO.: X-XK1PLM1S7-WA16-X
			SCALE PAGE REVISION N/A 2/2 A0

1

2

3

4