







RoHS



技术指标:

1. 工作温度: $-40^{\circ}\text{C} \sim 150^{\circ}\text{C}$.
2. 额定电压: 200V DC/AC(rms).
3. 额定电流: 2.0A AC, DC.
4. 接触电阻: $\leq 20\text{m}\Omega$.
5. 耐压值: 500V AC/minute.
6. 绝缘电阻: $\geq 1000\text{M}\Omega$.
7. 产品料号:



序号 (NO.)	品名 (Name)	材质 (Material)
①	2.00 F型立式2代WTB胶芯 2.00 Pitch S/T Wire To Board Housing(H=8.3)	LCP UL94V-0 本色 Natural
②	2.00 F型卧式2代WTB端子 2.00 Pitch R/A Wire To Board Terminal(H=5.2)	铜合金/表面镀锡 Copper Alloy/ Tin Plating
③	2.00 F型立式2代WTB焊片 2.00 Pitch S/T Wire To Board Fitting Nail(H=8.3)	铜合金/表面镀锡 Copper Alloy/ Tin Plating
④	2.00 F型立式2代WTB吸盖 2.00 Pitch S/T Wire To Board Cover(H=8.3)	LCP UL94V-0 本色 Natural



2 PIN 结构样式
(Structural style)

3 PIN 结构样式
(Structural style)

适用线路板 (PCB LAYOUT)



WITH COVER

CKT	DIM A	DIM B	DIM C	DIM D
2	2.00	4.90	8.00	2.50
3	4.00	6.90	10.00	2.50
4	6.00	8.90	12.00	3.50
5	8.00	10.90	14.00	5.50
6	10.00	12.90	16.00	7.50
7	12.00	14.90	18.00	9.50
8	14.00	16.90	20.00	11.50
9	16.00	18.90	22.00	13.50
10	18.00	20.90	24.00	15.50
11	20.00	22.90	26.00	17.50
12	22.00	24.90	28.00	19.50
13	24.00	26.90	30.00	21.50
14	26.00	28.90	32.00	23.50
15	28.00	30.90	34.00	25.50
16	30.00	32.90	36.00	27.50
17	32.00	34.90	38.00	29.50
18	34.00	36.90	40.00	31.50
19	36.00	38.90	42.00	33.50
20	38.00	40.90	44.00	35.50

OPERATION

X.X

±0.30

X.XX

±0.20

X.XXX

±0.10

Angle

±3°

DIM

TOL

DRAW

CHECK

APPROVE

SCALE

FIT

UNIT

mm

SIZE

A4

SHEET

1/1

PROJ.

◆

深圳市连盛精密连接器有限公司

PART NO.

1130300228

TITLE:

HY-NAWV

1

2

3

4

5

6

7

8

9