



RoHS

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.08.15	



3D View



Specifications(规格):

- 1.Impedance(特性阻抗) : 50Ω;
- 2.Frequency (工作频率) : DC~6GHz;
- 3.VSWR (电压驻波比) : 1.40 @2GHz;
1.50 @3GHz;
1.60 @6GHz;
- 4.Insulation resistance(绝缘阻抗) : ≥100MΩ;
- 5.Dielectric withstand voltage (介质耐电压) : 800V AC;
- 6.Mating cycles (耐久性) : ≥25 cycles;
- 7.Retention force latch(保持力) : ≥110N;
- 8.Temperature range(使用温度): -40℃~+105℃;
- 9.PART NO.:

XM0RLF4S7-NA06-X


Code: A~Z

10.Housing P/N:

XMHF4-PT05-X

Code: A~Z

BOM List:



RECOMMENDED CABLE STRIPPING DIM'S

5	XKS7-PBT02	Outer Ferrule	SUS		4 PCS	5K PCS/R
4	XMTF7-PBGN611	Center Conductor	Copper Alloy	Gold PLATED	4 PCS	5K PCS/R
3	XMBF7-PBT209	Outer Conductor	Copper Alloy	Tin PLATED	4 PCS	
2	XMHF4-PT15-X	Housing	PBT		1 PC	
1	XMC0-PTY04	Secondary Lock	PBT		2 PCS	
NO.	P/N	NAME	MATERIAL	FINISH (Contact)	Q'TY	Note

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn



XKB INDUSTRIAL PRECISION CO.,LIMITED

DESIGN	希文	VIEW:	MODEL TYPE: MINI FAKRA Female Connector for 302
CHECKED		UNIT: mm/in	PART NO.: XM0RLF4S7-NA06-X
APPROVED		SIZE: A4	DWG NO.: X-XM0RLF4S7-NA06-X
		SCALE	PAGE
		N/A	1/2
		REVISION	A0

A

A

B








B

C

C

D

D

Code List:							
Colde							
	A	B	C	D	E	F	Z
Color/RAL-No.	Black/9005	White/9001	Blue/5005	Bordeaux/4004	Green/6002	Brown/8011	Water Blue/5021
PART NO.	XMORLF4S7-NA06-A	XMORLF4S7-NA06-B	XMORLF4S7-NA06-C	XMORLF4S7-NA06-D	XMORLF4S7-NA06-E	XMORLF4S7-NA06-F	XMORLF4S7-NA06-Z

NOTE: ALL RIGHTS RESERVED,BANNED COPY!

ANGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	希文	VIEW: 	MODEL TYPE: MINI FAKRA Female Connector for 302
CHECKED		UNIT: mm/in	PART NO.: XMORLF4S7-NA06-X
APPROVED		SIZE: A4	DWG NO.: X-XMORLF4S7-NA06-X
			SCALE PAGE REVISION
			N/A 2/2 A0