

特性:

一.电气性能:EICTRICAL

- 1.额定电流:5.0A
- 2.接触阻抗:40 MILLIOHMS MAX
- 3.耐电压:100V AC / 1 mA MAX
- 4.绝缘阻抗:150V DC/100 MEGA OHMS MIN

二.机械性能:

- 1.插入力:5~20N
- 2.拔出力:8~20N
- 3.使用寿命:10000次.拔出力 6N MIN

三.材料:MATERIAL

四.电镀:FINISH

- 1.端子:接触点镀金1u"MIN
PIN脚焊接区域镀锡60U"MIN

- 2.外壳:镀镍50u"MIN (盐雾48H)

五.电镀品需做粘锡测试:粘锡面积达到95%以上.

六.SMT回流焊(峰值260°C±5°C)不能起泡.熔胶.变色不良(变形在公差范围以内)

七.工作温度:-55°C~+85°C





八.盐雾测试:通过48H在浓度为5±1%盐水的盐雾测试无生锈现象


A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12
GND			VBUS	CC1	D+	D-	SBU1	VBUS			GND
GND			VBUS	SBU2	D-	D+	CC1	VBUS			GND
B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1

BOM

序号	名称	用量	品名规格
1	外壳	1	Typec SUS304 T=0.30mm
2	Molding	1	Typec 16PIN Molding C7025 T=0.15 卡扣 SUS301 T=0.15mm LCP黑色

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd			
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: Type-C 16PIN 立插 L=6.5 双边脚		
			PAR	TYPEC-300D-BCP16H65	
DECIMALS:	ANGLES:		DWN	Lucas	
X.:±0.35	X'.:±4°		CHKD	Ethan	
X.X:±0.25	X.X'.:±3°		APVD	Jacob	
X.XX:±0.15			SCALE1:1	UNIT:MM	
		CUSTOMER COPY	SIZE:A4	SHEET:1F1	REV:A






200pcs/盘

10盘/扎X4
5盘/扎X2

10000PCS/箱

标签粘贴处



MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co., Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: Type-C 16PIN 立插 L=6.5 双边铆
DECIMALS:	ANGLES:		PAR TYPEC-300D-BCP16H65
X.:±0.35	X*.:±4°		DWN Lucas
X.X:±0.25	X.X*.:±3°		CHKD Ethan
X.XX:±0.15		CUSTOMER COPY	
		SCALE:1:1	UNIT:MM
		SIZE:A4	SHEET:1F1
			REV:A