



修订		标记	修改摘要	签名	日期
REV	MARK	REVISION	DESCRIPTION	SIGNATURE	DATE
AO			NEW DWG	黄艳兰	






2*06P~2*17P




2*04P



2*05P



A-A



8.6



7.23

NOTES:

1. Material: PBT, UL94V-0
2. Color: White
3. Current Rating: 2A AC,DC
4. Voltage Rating: 100V AC,DC
5. Temperature Rang: -40°C~+105°C
6. Contact Resistance: 20mΩ Max
7. Insulation Resistance: 500MΩ Min
8. Withstanding Voltage: 500V AC/minute

Poles	Dimension(mm)		
	A	B	C
2*04	4.50	10.30	8.75
2*05	6.00	11.80	8.75
2*06	7.50	13.30	10.25
2*07	9.00	14.80	11.75
2*08	10.50	16.30	13.25
2*09	12.00	17.80	14.60
2*10	13.50	19.30	14.60
2*11	15.00	20.80	15.60
2*12	16.50	22.30	16.60
2*13	18.00	23.80	16.60
2*14	19.50	25.30	16.60
2*15	21.00	26.80	16.60
2*16	22.50	28.30	16.60
2*17	24.00	29.80	16.60



深圳市华德共创科技有限公司

Shenzhen Huade co-create Technology Co.,LTD

电话: 0755-27111216 传真: 0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表			TITLE: 产品名称: MX1.5双排胶壳/503149	
X.X	±0.30	X.X* ±3°	APPD: 核准: 谢亮	PART NO: 产品编号: HDGC1502DHL-2XnP
X.XX	±0.20	X.XX* ±2°	CHECK: 校对: 王建业	DATE
X.XXX	±0.15	X.XXX* ±1°	DRAW: 绘图: 黄艳兰	SCALE
				UNIT
				CODE NUMBER
			1:1	mm
				A001