


Circuit Diagram



LED colour(LED颜色)	Part No. (料号)
Red(红色)/Blue(蓝色)	K6-6151S-23
Red(红色)/Jade green(翠绿)	K6-6151S-27
Yellow(黄色)/Jade green(翠绿)	K6-6151S-57
Blue(蓝色)/Jade green(翠绿)	K6-6151S-37

Rated Values: 30V DC 30mA;
 Contact Resistance: $\leq 0.05\Omega$;
 Dielectric Strength: 250V AC;
 Insulation Resistance: $\geq 100M\Omega$;
 Operating Force: 260±50gf;
 Life: 100,000 cycles;

②	Terminal	Phosphor bronze		Ag Plating		
①	Housing	PPA		Black		
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
APPROVALS		DATE		2021.3.29		
DRAWN	LIUCAN					
CHECKED						
APPROVALS						
TOLERANCES ARE		30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1
		10~30	±0.20		PROJ:	
		5~10	±0.15	±2°	DRAWING NO.	
		~ 5	±0.10		SHEET	1 OF 1

—	A	—	NEW	—	—	—
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.