












F		F		F	
修订 REV	标记 MARK	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE	
AO		NEW DWG	黄艳兰		



Poles	DIM(mm)				
	A	B	C	D	E
3	8.65	5.45	2.50	3.05	3.0
4	9.90	5.5	3.75	3.05	3.0
5	11.15	6.75	5.00	4.15	3.5
6	12.40	8.0	6.25	5.4	3.5
7	13.65	9.25	7.50	4.45	4.0
8	14.90	10.5	8.75	5.7	4.3
9	16.15	11.75	10.00	6.95	4.3
10	17.40	13.0	11.25	8.2	4.3
11	18.65	14.25	12.50	9.45	4.3
12	19.90	15.5	13.75	10.7	4.3
13	21.15	16.75	15.00	11.95	7.2
14	22.40	18.0	16.25	13.2	7.2
15	23.65	19.25	17.50	14.45	7.2
16	24.90	20.5	18.75	15.7	7.2
17	26.15	21.75	20.00	16.95	7.2
18	27.40	23.0	21.25	18.2	7.2
19	28.65	24.25	22.50	19.45	7.2
20	29.90	25.5	23.75	20.7	7.2



A-A

B-B

- Material:
Insulation:LCP,UL94V-0(Beige)
Pin:Phosphor Bronze/Tin-Plated
Tab:Phosphor Bronze/Tin-Plated
- Current Rating: 1A AC,DC
- Voltage Rating: 150V AC,DC
- Temperature Rang: -40°C~+105°C
- Contact Resistance: 20mΩ Max
- Insulation Resistance: 500MΩ Min
- Withstanding Voltage: 500V AC/minute
- Glow-Wire Flammability: 750°C



深圳市华德共创科技有限公司

Shenzhen Huade co-create Technology Co.,LTD

电话: 0755-27111216 传真: 0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表		TITLE: 产品名称: 12507WR-HNNG	
X.X ±0.30	X.X* ±3°	APPD: 核准: 谢亮	PART NO: 产品编号: 12507WR-HNNG-HDGC
X.XX ±0.20	X.XX* ±2°	CHECK: 校对: 王建业	DATE
X.XXX ±0.15	X.XXX* ±1°	DRAW: 绘图: 黄艳兰	SCALE
			UNIT
			CODE NUMBER
			A001