







修订 REV	标记 MARK	修改摘要 REVISION DESCRIPTION	F	
			签名 SIGNATURE	日期 DATE
AO		NEW DWG	黄艳兰	



A-A



Poles	DIM(mm)		
	A	B	C
2	1.25	4.05	4.05
3	2.50	5.30	5.30
4	3.75	6.55	6.55
5	5.00	7.70	7.80
6	6.25	8.95	9.05
7	7.50	10.20	10.30
8	8.75	11.45	11.55
9	10.00	12.70	12.80
10	11.25	13.95	14.05
11	12.50	15.20	15.30
12	13.75	16.45	16.55
13	15.00	17.70	17.80
14	16.25	18.95	19.05
15	17.50	20.20	20.30
16	18.75	21.45	21.55

NOTES:

1. Material: Nylon66, UL94V-0
2. Color: Natural(White)
3. Current Rating: 1A AC,DC
4. Voltage Rating: 150V AC,DC
5. Temperature Rang: -25°C~+85°C
6. Contact Resistance: 20mΩ Max
7. Insulation Resistance: 1000MΩ Min
8. Withstanding Voltage: 500V AC/minute



深圳市华德共创科技有限公司

Shenzhen Huade co-create Technology Co.,LTD

电话: 0755-27111216 传真: 0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表				TITLE: 产品名称: 12507WS-HNNG			
X.X	±0.30	X.X*	±3°	APPD: 核准: 谢亮	PART NO: 产品编号: 12507HS-HNNG1-HDGC		
X.XX	±0.20	X.XX*	±2°	CHECK: 校对: 王建业	DATE	SCALE	UNIT
X.XXX	±0.15	X.XXX*	±1°	DRAW: 绘图: 黄艳兰		1:1	mm
							CODE NUMBER A001