






RoHS


REV	ECN NO.	DESRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	更新图框			2025.11.19



后视图



特性: Specifcations:
电器: Electrical:
接触阻抗: Contact Resistnce 30 milliohms Max
耐电压: Dielectric Wihsanding Volage:150V AC Sea Levol
绝缘阻抗: Insulatin Resistance:100 MEGA ohms MIN
材料: Matorial:
塑胶Housing:Hng Temperature Thermoplastics.LCP UL94V-0 Black
端子: Contact:Copper Alloy铜合金铜壳 T=0.2mm
电镀Finish:端子Contact:Gold plating on contact area, tin plating on welding feet
接触区域镀金1U 焊脚镀锡
外壳:shell:SPCC T=0.5mm
电镀Finish:外壳:shell 铜底50u 表面镀金1u或者镀镍100-150u



PCB LAYOUT
Tolerance ±0.05

X. 0.3	X.°±
. X±0.2	.X°±
. XX±0.08	.XX°±
. XXX±0.03	.XXX°±
UNITS:	mm

THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF XFCN AND SHALL
NOT BE REPRODUCED, COPIED OR CUED IN
ANY MANNER WITHOUT THE PRIOR
WRITTEN CONSENT OF XFCN

PART NO: HDMI-A-19F-S-D		XFCN 兴飞连接器		
TITLE: HDMI A型 19P/F SMT+DIP		0769-82001899		
		www.xfconn.com		
		DWG NO: /		
APPD	Chen ZhiQiang	VIEW		
CHKD	Liu Wei	SCALE		SHEET
DRAW	Chen HongJiang	SCALE		REV
DATE	2025.11.19	NONE		1/1 A1