




TOLERANCE: ± 0.05 , THICKNESS: 1.6mm
RECOMMENDED PCB LAYOUT

NOTE:

1. MATERIAL:

- 1.1 HOUSING: PPS
- 1.2 CONTACT: COPPER ALLOY
- 1.3 NUT: SUS

2. FINISH:



2.1 CONTACT:

GOLD PLATING ON CONTACT AREA
NICKEL UNDER PLATING OVERALL



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ± 0.30 X.XX ± 0.25 X.XXX ± 0.15 X.' $\pm 2'$ X.X' $\pm 0.5'$	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: M80 26pin 板端	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW-M80F-26P-310B	MOLD NO.
	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HYC-2511171125	SHEET NO. 1 OF 1
			SCALE:1:1 SIZE: A4	



 深圳市华宇创精密电子有限公司			
TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.' ±2" X.X' ±0.5"	DRAWN BY :	DATE :	PART NAME:
	陈一鸣	2014-02-23	M80
 UNIT: mm [inch] SCALE:1:1 SIZE: A4	CHECKED BY:	DATE :	PART NO.
	马跃	2014-02-23	MOLD NO.
	APPROVED BY:	DATE :	DRAW NO:
	邱敏	2014-02-23	SHEET NO. 1 OF 1