



未注公差/General tolerances(mm)													D 0.1/10	
0	>3	>6	>10	>18	>30	>50	>80	>120	>180	>250	>315	>400		>500
~	3	6	10	18	30	50	80	120	180	250	315	400	500	≤ ±2°
±0.12	±0.18	±0.22	±0.26	±0.31	±0.37	±0.57	±0.80	±0.93	±1.05	±1.15	±1.60	±2.20	±2.50	

REV	ECN	DESCRIPTION	DFT	DATE

A



B



C

DB14H — 13.5 — XXP — C — S/P
(Series No.) (Pitch) (Poles) Slotted/Phillips
(Color):GN:(Green), BK:(Black), BU:(Blue), RD:(Red), GY:(Gray)
OG:(Orange), WT:(White), YL:(Yellow), CR:(Clear)

C

D

UL 标准/UL Standard:	B	C	D
额定电压/电压/Rated Voltage(V)/Current(A)	800/50	/	/
IEC 标准/IEC Standard:			
额定电压/电压/Rated Voltage(V)/Current(A)		750/57	
螺栓扭矩/Torque Tightening(N·m/Lb·in)		M4 1.2N·m/10.8Lb·in	
线径范围(裸线/导线)/Wire Range(Rigid and flexible)(mm²/AWG)		10.0/20-8	
间距/Pitch(mm)/线距范围/Poles		13.5/01-12	
剥线长度/Stripping length(mm)		/	
使用温度范围/Operating temperature(°C)		-40~+105	
符合RoHS标准要求/Conform to RoHS		Yes	

D

MAT NO.:	/	ORABO	宁波地博电气有限公司
STATUS:	/	NINGBO DORABO ELECTRICAL CO., LTD	
APPD: Jting Chen 2025.05.29	NAME:	DB14H-13.5-XXP-C-S	
CHKD: Duck Mao 2025.05.29	DRAWING NO.:	/	
DFT: Steven Lu 2025.05.29	TYPE: CUSTOMER_DRAWING	SCALE: 1:1	REV M1
SIZE: A4	100mm	1/1	

1

2

3

4

5

6