









RoHs

VER	MARK	PR. BY	ECR/ECN	DESCRIPTION	DATE
A		Li		NEW RELEASE	12/21' 20



A5	CC1	B5	CC2
A9	VBUS	B9	VBUS
A12	GND	B12	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME



SPECIFICATION:

1. Material:

HOUSING&MOLDING:HIGH TEMPERATURE RESISTANT PLASTIC,UL94 V-0
CONTACTS:COPPER ALLOY
SHELL:SUS304,T=0.30

2. Mechanical:

- 2.1.Mating force:5~20Nf Max.;
- 2.2.Unmating force:6~20Nf Min.;
- 2.3.Durability:10000 Cycles;

3. Electrical:



- 3.1.Current Rating:3A Max.;
- 3.2.Voltage Rating:20V Max.;
- 3.3.Dielectric Withstanding voltage:100VAc;
- 3.4.Contact resistance:40m Ohms Max.;
- 3.5. Insulation Resistance:100M Ohms Min.;

4. Environmental:

- 4.1.Operating temperature:-40° C~+85° C;
- 4.2. Wetting Temperature:265±5° C, 5±0.5s

Recommend PCB Layout
(Tol:±0.05,T=1.0±0.05mm)

CUSTOMER		GENERAL TOLERANCES UNLESS SPECIFIED		APPROVED BY: Liang		TITLE: TYPE-C母座 6P 四脚插板 LCP 黑色 镀亮镍 长脚0.95 体长6.8 带中夹片		深圳市辉焕科技有限公司	
SIZE A4	UNITS MM[INCH]	X±0.50 .X±0.35	X*±5.0° .X*±3.0°	CHECKED BY: Cao		PART NO.: HH 6P TYPE-C(Y005)			
SCALE 1:1	REV. A	.XX±0.25 .XXX±0.15	.XX*±2.5° .XXX*±2.0°	DESIGN BY: Li		DWG NO.: HH 6P TYPE-C(Y005)		SHEET 1/2	



1. 每卷前后各空16PCS, 尾部用美纹胶纸封住;
2. 将产品放满盘后, 再卷一圈保护带, 用美纹胶纸将其封住, 并贴上1Pcs物料标签;
3. 每15卷盘一叠共15000Pcs装入1个外箱内;
4. 在搬运过程中要轻拿轻放;
5. 在运输中不可堆放过多(1.8M最高), 不可重压;
6. 跌落测试条件:
成品箱从1.2米高度自由落体(一角三棱六面):
 - a. 产品不可跑出下带凹槽;
 - b. 产品不可有摔伤, 变形;
 - c. 内包装材料不可严重破损.

NO.	NAME	SPEC	Q' TY
①	TYPE C RECEPTACLE		15000PCS/CARTON
①	CARRIER TAPE	W=16mm, T=0.40mm	1000PCS/PLATE
②	COVER TAPE	W=13.2mm	15PLATES/CARTON
③	REEL PLATE	ø330*100*16.4mm	15PCS/CARTON
④	RoHS LABEL		15PCS/CARTON
⑤	PRODUCT LABER		15PCS/CARTON
⑥	CARTON	340*340*325mm	1PCS/PACKAGE

PACKAGING		GENERAL TOLERANCES UNLESS SPECIFIED		APPROVED BY: Liang	TITLE: TYPE-C母座 6P 四脚插板 LCP 黑色 镀亮镍 长脚0.95 体长6.8 带中夹片	深圳市辉焕科技有限公司	
SIZE A4	UNITS MM[INCH]	X±1.0 .X±0.50	X*±5.0* .X*±3.5*	CHECKED BY: Cao	PART NO.: HH 6P TYPE-C(Y005)		
SCALE 1:1	REV. A	.XX±0.30	.XX*±2.5*	DESIGN BY:	DWG NO.:	SHEET 2/2	
		.XXX±0.15	.XXX*±1.5*	Li	HH 6P TYPE-C(Y005)		