








RoHS+REACH



>4P

2P&3P



PCB LAYOUT

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: -25° C~85° C.
3. 额定电压: 50V, AC/DC.
4. 接触电阻: ≤40mΩ.
5. 绝缘电阻: ≥100MΩ.
6. 额定电流: 1A , AC/DC.

| CKT | DimA  | DimB  | DimC  |
|-----|-------|-------|-------|
| 2   | 1.25  | 4.50  | 7.50  |
| 3   | 2.50  | 5.75  | 8.75  |
| 4   | 3.75  | 7.00  | 10.00 |
| 5   | 5.00  | 8.25  | 11.25 |
| 6   | 6.25  | 9.50  | 12.50 |
| 7   | 7.50  | 10.75 | 13.75 |
| 8   | 8.75  | 12.00 | 15.00 |
| 9   | 10.00 | 13.25 | 16.25 |
| 10  | 11.25 | 14.50 | 17.50 |
| 11  | 12.50 | 15.75 | 18.75 |
| 12  | 13.75 | 17.00 | 20.00 |
| 13  | 15.00 | 18.25 | 21.25 |
| 14  | 16.25 | 19.50 | 22.50 |
| 15  | 17.50 | 20.75 | 23.75 |

| 序号 | 项目 | 描述  | 备注 |
|----|----|-----|----|
| 1  | 塑胶 | LCP |    |
| 2  | 端子 | 黄铜  |    |
| 3  | 焊片 | 黄铜  |    |
|    |    |     |    |

|      |      |             |         |
|------|------|-------------|---------|
| 6.0  |      |             |         |
| 5.0  |      |             |         |
| 4.0  |      |             |         |
| 3.0  |      |             |         |
| 2.0  |      |             |         |
| 1.0  |      |             |         |
| REV. | DATE | DESCRIPTION | DRAWING |

|                     |                                                                                             |             |
|---------------------|---------------------------------------------------------------------------------------------|-------------|
| DRAWING:<br>Frank   | GENERAL TOLERANCE<br>.X:=±0.30 .X°:=±2°<br>.XX:=±0.20 .XX°:=±1°<br>.XXX:=±0.10 .XXX°:=±0.5° |             |
|                     |                                                                                             |             |
| CHECKED:<br>yangjie | UNIT: MM                                                                                    | PROJECTION: |
|                     | SCALE: 1/1                                                                                  |             |
| APPROVAL:           | SHEET: 1/1                                                                                  |             |

**CHIN-BAN**  
Electronic Technology

|                                             |          |
|---------------------------------------------|----------|
| DESCRIPTION: 1.25mm Wire To Board Wafer SMT |          |
| PART NO:                                    | REV: 1.0 |
| OLD CODE: WF125UR-XXX-01                    |          |
| DRAWING NO:                                 | SIZE: A4 |