





RoHS



PCB LAYOUT

Technical Data

Material:

Contact Material:Copper Alloy

Contact Plating: Au or Sn Over Ni

Insulator Material:PPS UL94V-0

Electrical:

Rating current:1Amps/contact max

Rating voltage:60V AC/DC

Contact resistance:≤10mΩ/contact

Insulation resistance:≥1000MΩ

withstanding Voltage:500V AC/minute

Mechanical:

Operaing temperatures:-40℃ to +105℃

Soldering temperature:+255℃ MAX(PPS)

Ordering Code:

MH127V-11-XX-H22-0820

1 2

1.序列号

2.Pin位数: 02-50P

X.±0.50	X.°±	PART NO: MH127V-11-06-H22-0820		XFCN 兴飞连接器		
.X±0.25	.X°±					
.XX±0.15	.XX°±	TITLE: 1.27mm Machined Pin Header		0769-82001899		
.XXX±0.10	.XXX°±			www.xfconn.com		
UNITS:	mm			DWG NO: /		
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN		APPD	Chen ZhiQiang			
		CHKD	Liu Wei	VIEW		
		DRAW	Chen HongJiang	SCALE	SHEET	REV
		DATE	2025.11.21	NONE	1/1	A1