




REV.	DESCRIPTION	APPD	DATE

产品规格:

- 1 材质
- 1.1 胶芯: 高温尼龙
- 1.2 端子: 黄铜镀锡
- 2 电气性能
- 2.1 额定电压 250V AC、DC
- 2.2 额定电流 3A AC、DC
- 2.3 接触阻抗 < 30 mΩ
- 2.4 绝缘阻抗 > 1000MΩ
- 2.5 耐压 > 1000 V AC

	DIM A	DIM B	DIM C
6 P	8.00	6.90	3.00
8 P	10.00	8.90	3.00
10 P	12.00	10.90	5.00
12 P	14.00	12.90	7.00
14 P	16.00	14.90	9.00
16 P	18.00	16.90	11.00
18 P	20.00	18.90	13.00
20 P	22.00	20.90	15.00

PHBXX-00F1-2002-A

- 1 1.6针长
- 2 1.8针长
- B1 亮锡针
- T1 雾锡针
- F1 金针
- XX = pin 数

PART NO: PHBXX-00F1-2001-A		MATERIAL:			
LOT NO:		FINSH:			
UNIT: MM	SIZE: A4	COLOR:			
TOLERANCES: X. X=±0.35 X. XX=±0.25 X. XXX=±0.15 GENERAL ANGLE: X. X=±3.0° X. XX=±2.0°		TITLE:			
		PHB双排针座 立插 短针			
		DR: 刘 静		REV: A	
		CHK: 刘 静		DWG NO: FP-090012	
APP: 刘 静		SCALE: 1:1		SHEET: 1 OF 1	
					