









RECOMMENDED P.C.B. PATTERN LAYOUT



RECOMMENDED FPC/FFC DIMENSION

- Note:
- Material:
 - Housing: thermoplastic high temp.UL94V-0; Color: natural.
 - Latch: thermoplastic high temp.UL94V-0; Color: black.
 - Terminal: copper alloy.
 - Fitting Nail: copper alloy.
 - Finish:
 - Terminal:

C:Matt-tin 90~120u" on contact and solder area
50~100u" Nickel under plating over all.

I:Gold 1u" on contact and solder area
50~100u" Nickel under plating over all.
 - Fitting Nail:

C:Matt-tin 90~120u" over all
50~100u" Nickel under plating over all.
 - Product must comply HF RoHS specification.

4. Product No:

AFC01-S **

CKTS **

CONTACTS TYPE

F:Lower

PLATING

C:Matt-Tin,

I:Gold 1u"

F

*

*

-

**

REMARKS

HF:Halogen free

OU:CARRIER,

UNILATERAL HOLE

PACKING

A:Tape&Reel

C:Tube

CKTS	DIM A	DIM B	DIM C
4	1.50	2.60	6.40
5	2.00	3.10	6.90
6	2.50	3.60	7.40
7	3.00	4.10	7.90
8	3.50	4.60	8.40
9	4.00	5.10	8.90
10	4.50	5.60	9.40
11	5.00	6.10	9.90
12	5.50	6.60	10.40
13	6.00	7.10	10.90
14	6.50	7.60	11.40
15	7.00	8.10	11.90
16	7.50	8.60	12.40
17	8.00	9.10	12.90
18	8.50	9.60	13.40
19	9.00	10.10	13.90
20	9.50	10.60	14.40
21	10.00	11.10	14.90
22	10.50	11.60	15.40
23	11.00	12.10	15.90
24	11.50	12.60	16.40
25	12.00	13.10	16.90
26	12.50	13.60	17.40
27	13.00	14.10	17.90
28	13.50	14.60	18.40
29	14.00	15.10	18.90
30	14.50	15.60	19.40
31	15.00	16.10	19.90
32	15.50	16.60	20.40
33	16.00	17.10	20.90
34	16.50	17.60	21.40
35	17.00	18.10	21.90
36	17.50	18.60	22.40
37	18.00	19.10	22.90
38	18.50	19.60	23.40
39	19.00	20.10	23.90
40	19.50	20.60	24.40
41	20.00	21.10	24.90
42	20.50	21.60	25.40
43	21.00	22.10	25.90
44	21.50	22.60	26.40
45	22.00	23.10	26.90
46	22.50	23.60	27.40
47	23.00	24.10	27.90
48	23.50	24.60	28.40
49	24.00	25.10	28.90
50	24.50	25.60	29.40
51	25.00	26.10	29.90
52	25.50	26.60	30.40
53	26.00	27.10	30.90
54	26.50	27.60	31.40
55	27.00	28.10	31.90
56	27.50	28.60	32.40
57	28.00	29.10	32.90
58	28.50	29.60	33.40
59	29.00	30.10	33.90
60	29.50	30.60	34.40

CUSTOMER DRAWING

Tolerance Unspecified (未注公差)	Size(图幅): A4
0.0 ±0.15 0° ±5°	Unit(单位): MM
0.00 ±0.10 0° ±3°	Scale(比例): 1:1
0.000 ±0.05 0° ±1°	Project View (投影视角): 1 OF 1
	Page(页数): A
	Rev(版本): A



连兴旺电子(深圳)有限公司
LXWCONN ELECTRONICS (SHENZHEN) CO., LTD

Product Name(产品名称):
0.5Pitch H=2.0 FPC Easy-on R/A Type1 SMT CONN


Product No(产品料号):
AFC01-S**F***

Designer(设计):
Allan

Checked(审核):

Approved(核准):

Rev 版本	初版发行 变更内容	2011/03/23 日期	Allan Revisor 制/修订人
-----------	--------------	------------------	---------------------------




NOTES:

1. 10 SPROCKET HOLE PITCH CUMULATIVE TOLERANCE.±0.20mm
2. CARRIER CAMBER NOT TO EXCEED 1mm IN 250mm.
3. ALL DIMENSIONS MEET EIA-481-C REQUIREMENTS.
4. MATERIAL: XXXXX ANTI-STATIC POLYSTYRENE.
5. THICKNESS: 0.35 ± 0.05 mm.
6. PACKING LENGTH PER 13" REEL : 24.60METERS.
7. COMPONENT LOAD PER 13" REEL : 2000PCS.
8. PEELING OFF FORCE OF TOP TAPE 0.1N~0.7N(10.2gf~71.4gf).

EB-650XX230-XX

└── 00: 黑色
 01: 白色



CKTS	BO ± 0. 10	W	W1	F	SO ± 0. 10
4	6. 70	16±0. 3/-0	16. 4	7. 5 ± 0. 10	
5	7. 20				
6	7. 70				
7	8. 20				
8	8. 70				
9	9. 20				
10	9. 70				
11	10. 20				
12	10. 70				
13	11. 20				
14	11. 70				
15	12. 20				
16	12. 70	24±0. 3/-0	24. 4	11. 5 ± 0. 10	单边孔
17	13. 20				
18	13. 70				
19	14. 20				
20	14. 70				
21	15. 20				
22	15. 70				
23	16. 20				
24	16. 70				
25	17. 20				
26	17. 70				
27	18. 20				
28	18. 70				
29	19. 20				
30	19. 70				
31	20. 20				
32	20. 70				
33	21. 20				
34	21. 70				
35	22. 20				
36	22. 70				
37	23. 20				
38	23. 70				
39	24. 20				
40	24. 70				
41	25. 20				
42	25. 70				
43	26. 20				
44	26. 70	44 ± 0. 30	44. 4	20. 2 ± 0. 15	40. 4
45	27. 20				
46	27. 70				
47	28. 20				
48	28. 70				
49	29. 20				
50	29. 70				
51	30. 20				
52	30. 70				
53	31. 20				
54	31. 70				
55	32. 20				
56	32. 70				
57	33. 20				
58	33. 70	56 ± 0. 30	56. 4	26. 2 ± 0. 15	52. 4
59	34. 20				
60	34. 70				

CLASSIFICATION DIMENSION(尺寸类别):
FAI(首次检验): ③③ To ③③
"■" MARK IS MAJOR DIM(重点尺寸标示)
"⊙" MARK IS CRITICAL DIM(Cpk&Cp标示)

Tolerance Unspecified (未注公差)	Size(图幅): A4
0.0 ±0.10 0°. ±3°	Unit(单位): MM
0.00 ±0.05 0° 0 ±2°	

0.000 ±0.02 0° 0.00 ±1°	Scale(比例): 1 : 1
Project View (投影视角)	Page(页数): 1 OF 1
	Rev(版本): 2.0

 连兴旺电子(深圳)有限公司
LXWCONN ELECTRONICS (SHENZHEN) CO., LTD

示)	Product Name(产品名称):
:	0.5Pitch H=2.0 FPC 掀盖卧式SMT型, 载带

Product No(产品料号):	EB-650XXX230-XX
-------------------	-----------------

Drawing No(图面编号):	Date(日期):
DNE00001-1	2019/03/30

Designer(设计): 吴小光	Checked(审核):	Approved(核准):
----------------------	--------------	---------------

2.0	新增白色载带规格	2019/03/30	吴小光
1.0	初版发行	2011/04/15	Allan
Rev 版本	Change Description 变 更 内 容	Date 日 期	Revisor 制/修订人