





RoHS


序号	品名	材质
①	ZH1.5直针WTB胶芯	PA66 UL94V-0 米色 白色
②	ZH1.5直针WTB端子	铜合金/表面镀锡




TYPE 1(无K脚)



TYPE 2(打K脚)




SECTION A-A



CKT	A	B	CKT	A	B
2	1.5	4.5	12	16.5	19.5
3	3.0	6.0	13	18.0	21.0
4	4.5	7.5	14	19.5	22.5
5	6.0	9.0	15	21.0	24.0
6	7.5	10.5	16	22.5	25.5
7	9.0	12.0	17	24.0	27.0
8	10.5	13.5	18	25.5	28.5
9	12.0	15.0	19	27.0	30.0
10	13.5	16.5	20	28.5	31.5
11	15.0	18.0			

技术指标(Technical Index):

- 温度范围(Temperature range): -25° C~+85° C.
- 额定电压(Rated voltage): 100V, AC.
- 额定电流(Rated current): 1.0A AC, DC.
- 接触电阻(Contact resistance): ≤20mΩ .
- 绝缘电阻(Insulation resistance): ≥500MΩ.
- 耐压值(Withstanding voltage): 500V AC/minute.
- 产品料号(Product material No.):



				OPERATION		DRAW			SCALE	FIT	深圳市连盛精密连接器有限公司	
				X.X	±0.30				UNIT	mm		
				X.XX	±0.20	CHECK			SIZE	A4	PART NO.	1130700017
				X.XXX	±0.10				SHEET	1/1		
REV	DATE	MODIFICATION	DESCRIPTION	CHANGE	Angle	APPROVE			PROJ.		TITLE:	ZH-NA
					DIM							