








[illegible][illegible][illegible]

								8	9								
RoHS								序号	品名	材质							
								①	ZH1.5直针WTB胶芯	PA66 UL94V-0 米色 白色							
								②	ZH1.5直针WTB端子	铜合金/表面镀锡							
F																	
E																	
D																	
C	技术指标(Technical Index): - 温度范围(Temperature range): -25° C~+85° C. - 额定电压(Rated voltage): 100V, AC. - 额定电流(Rated current): 1.0A AC, DC. - 接触电阻(Contact resistance): ≤20mΩ . - 绝缘电阻(Insulation resistance): ≥500MΩ. - 耐压值(Withstanding voltage): 500V AC/minute. - 产品料号(Product material No.):																
B																	
A	适用线路板(PCB LAYOUT)																
				OPERATION		DRAW		SCALE		FIT							
				X.X	±0.30			UNIT	mm	深圳市连盛精密连接器有限公司							
				X.XX	±0.20	CHECK		SIZE	A4								
				X.XXX	±0.10			SHEET	1/1								
REV				DATE	MODIFICATION DESCRIPTION	CHANGE	APPROVE	PROJ.	◆		PART NO. TITLE:	1130700013 ZH-NA					
1		2		3		4		5		6		7		8		9	

[illegible][illegible][illegible]

- [illegible]

[illegible]